






PCB Layout

POLE		2	3	4	5	6	7	8
A		25.00	40.00	55.00	70.00	85.00	100.00	115.00
B		15.00	30.00	45.00	60.00	75.00	90.00	105.00
Tol.		±0.15			±0.25			
POLE	9	10	11	12	13	14	15	16
A	130.00	145.00	160.00	175.00	190.00	205.00	220.00	235.00
B	120.00	135.00	150.00	165.00	180.00	195.00	210.00	225.00
Tol.	±0.35				±0.50			

SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item ① Insulator(housing): Thermoplastic (UL94V-0)
- Item ② Wire guard: Stainless steel
- Item ③ Terminal Body(contact pin): Copper.Tin platd
- Item ④ With flange left cover: Thermoplastic (UL94V-0)
- Item ⑤ With flange right cover: Thermoplastic (UL94V-0)
- Item ⑥ Pad board: Thermoplastic (UL94V-0)

- Electrical:
- | | |
|--------------------------|------------------------|
| cULus | IEC |
| ● Voltage rating: | 600V 1000V |
| ● Current rating: | 37A 76A |
| ● Wire range: | 0.2-16 mm ² |
| ● Solid wire(AWG): | 6-24 |
| ● Stranded wire(AWG): | 6-24 |
| ● Wire strip length: | 12-13mm |
| ● Withstanding Voltage: | 2.2KV 8KV |
| ● Operating temperature: | -40°C to +115°C |
| ● Soldering temperature: | 250°C±10°C/5 Sec |
| ● Safety Approval: | |



H8 xx 1 0 x 1 xxxx G

No. OF POLES
02: 2 POLES
:
08: 8 POLES

COLOR
0: BLACK
5: GREEN
6: BLUE
8: GREY

G: Pb<40000ppm

0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		H8 15.0mm W/Flange Series						
PART NO.		H8xx10x1xxxxG			DWG NO.	8H80005		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance	
		Runner 2010.10.15	Tony 2007.06.21		UNIT: mm	X. ±0.50		
						X.X ±0.30		
					SHEET: 01/01	REV.: B	X.XX ±0.10	
X° ±1°								