

1	2	3	4	5	6	7
				SIGN	DATE	DESCRIPTION
				△	7/23'08	With flange type is changed
				△	7/23'08	Operating temperature is changed
				△	04/20'09	The design is changed
				△	11/17'09	The design is changed from the round hole to hexagonal hole
				△	01/12'10	Add cULus standard
				△	03/31'10	Add the 2p mark
				△	04/28'12	Flange Nut is changed
				△	04/28'12	Add the cutaway view
				△	04/28'12	The dimensions are added
				THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!		

Materials

Item a Terminal housing:Thermoplastic (UL94V-0)

Item b Female contact:PhBz(CuSn), Tin plated

Item c Terminal cover:Thermoplastic (UL94V-0)

Item d Flange Nut:Brass M2.5

Electrical

- Voltage rating: 300VAC
- Current rating: 10A
- Withstanding Voltage: 1.6kv
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: 
- Critical dimension: 

V7 xx 7 2 x 1 xxxx G

No. OF POLES

02 2 POLES

03 3 POLES

... ..

24 24 POLES

Color

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)

G RoHS compliant
(lead<4%)
In copper Alloy

0000: "@" Logo (Standard)

000A: "ANYTEK" Mark

Any special item by
customer request.
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		V7 5.0 Series Right angle (With flange)				
PART NO.	V7xx72x1xxxxG				DWG NO.	8V70203
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance	
		Guoxue 2012.04.28	Guoxue 2012.04.28		UNIT: mm	X. ±0.5
					SCALE: NONE	X.X ±0.3
						X.XX ±0.1
						X° ±1°
SHEET: 01/01		REV.: H				