


Recommended PANEL CUTOUT
MAX. PANEL THICKNESS 8mm

▲ SWITCH FUNCTION

POS. 1	POS. 2
1-2 ON 3-4 OFF	1-2 (OFF) 3-4 (ON)




RED +
GREEN +
BLUE + (-)

▲ SPDT ON-(OFF) / OFF-(ON)
CONTACT CONFIGURATION
() = MOMENTARY FUNCTION

() = MOMENTARY FUNCTION



NOTE:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- TERMINAL NOS. FOR REF. ONLY
- RATING: 2A @ 48VDC
- CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
- INSULATION RESISTANCE: 1,000MΩ @ 500VDC
- DIELECTRIC STRENGTH: 2,000VAC MIN. FOR 1 MINUTE
- ELECTRICAL LIFE: 50,000 CYCLES
- OPERATING TEMPERATURE: -20°C to 55°C
- ACTUATION FORCE: 4N
- INGRESS PROTECTION: IP65
- ▲ DENOTES CRITICAL PARAMETER
- ▲ 13. HARDWARE INCLUDED (NOT SHOWN) HEX NUT AND O-RING
- ▲ 14. ILLUMINATION VOLTAGE: 24V



▲ DOT ILLUMINATION
COLOR: RGB
(RED / GREEN / BLUE)


▲ ACTUATOR
BLACK ANODIZED




▲ BODY
BLACK ANODIZED

25.7±1.0
[1.01±.04 in]

36.0±1.0
[1.42±.04 in]



M22x1.0



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
A	ECO-101228	Release	09/08/22	MW	TITLE PV7F2Y011-2R5				100122693
					SCALE	DATE	DR	DWG	REV
					1:1	9/1/2022	MW	52-PV7F2Y0112R5	A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED