


Technical drawing of a mechanical part showing a top view and a side view. The top view shows a rectangular plate with four vertical slots and four vertical pins. The side view shows the profile of the plate with a height of 7.7 and a width of 8.3. Dimensions include Dim L, Dim A, 0.80, 7.7, and 8.3. A dashed line indicates a curved path through the slots.



DIM		TOL		
		2P-6P	7P-12P	13P-16P
Dim L	(N+2)×7.62	±0.15	±0.20	±0.30
Dim A	N×7.62	±0.15	±0.20	±0.30
Dim B	(N-1)×7.62	±0.15	±0.20	±0.30
Dim C	(N+1)×7.62	±0.15	±0.20	±0.30

SIGN	DATE	DESCRIPTION	APPROVER
	2010.01.30	The material is changed from Brass to Copper	Jacke
	2010.01.30	The Part No is changed	Jacke
	07/31`12	Added TUV standard	Chen Bo
	07/31`12	The Dimension is added	Chen Bo
	07/31`12	The IEC spec is removed	Chen Bo
	07/31`12	Soldering temperature changed from 250°C±10°C/5Sec to 260°C± 5°C/5Sec	Chen Bo
<i>THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!</i>			

- Item ① Terminal(housing): Thermoplastic (UL94V-0)
- Item ② Male contact pin: Copper Tin plated

	Electrical	cULus	TUV
●	Voltage rating:	300V	800V
●	Current rating:	20A ¹⁾ 32A ²⁾	32A
●	Withstanding Voltage:	1.6KV	6KV
●	Operating temperature:	-40°C to +115°C	
	● Soldering temperature:	260°C± 5°C/5 Sec	
	● Safety Approval:		
●	Critical dimension:		

$\triangle_2$ VC xx 02 x 1 xxxx G

Solid Block
02 2 POLES
03 3 POLES

16 16 POLES

COLOR

0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)

— G RoHS compliant
(lead<4%)
In copper Alloy

— 000 0 Standard @ Logo
000 A Standard ANY Logo
Any special item by
customer request,
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		VC 7.62 SERIES (Feed-through header with slip-on connection)					
PART NO.		VCxx02x1xxxxG		DWG NO.		8VC0005	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Chen Bo 07/31/12	Chen Bo 07/31/12			UNIT: mm	X. ±0.50
						SCALE: NONE	X.X ±0.30
				SHFFT: 01/01		REV: D	X.XX ±0.10
							X° ±1°