




P.C.B. LAYOUT

N = Number of poles
 Dim A=(N-1)x3.81+2.8
 Dim B=(N-1)x3.81
 Dim C=(N-1)x3.81+14.2
 Dim D=(N-1)x3.81+9.0
 Dim E=(N-1)x3.81

	Dim A	Dim B	Dim C	Dim D	Dim E
2-5p	±0.10	±0.10	±0.10	±0.10	±0.10
6-10p	±0.15	±0.15	±0.15	±0.15	±0.15
11-15p	±0.20	±0.20	±0.20	±0.20	±0.20
16-20p	±0.25	±0.25	±0.25	±0.25	±0.25
21-24p	±0.30	±0.30	±0.30	±0.30	±0.30

SIGN	DATE	DESCRIPTION	APPROVER
△	7/23'08	With flange type is changed	Marvin
△	7/23'08	Operating temperature is changed	Marvin
△	11/14`09	The design is changed from the round hole to hexagonal hole.	Jacke
△	01/12`10	Add cULus standard	Jacke
△	08/10`13	change the dimension from 0.93 to 1.07	Chen Bo
△	08/10`13	update the drawing	Chen Bo
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Materials

Item a Terminal body:Thermoplastic (UL94V-0)

Item b Female contact:PhBz(CuSn), Tin plated

Item c With Flange Nut :Brass M2.5

Electrical

- Voltage rating: 300V AC
- Current rating: 8A
- Withstanding Voltage: 1.6kv
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval:

V7 xx 3 2 x 0 xxxx G

No. OF POLES
 02 2 CONTACTS
 03 3 CONTACTS
 ...
 24 24 CONTACTS

G RoHS compliant
 (lead<4%)
 In copper Alloy

0000: "@" Logo (Standard)
 000A: "ANYTEK" Mark
 Any special item by
 customer request.
 please contact sales
 department.

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)
- 9 White(RAL1102)
- C Green(RAL6018/U)

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		V7 3.81 series Vertical With flange			
PART NO.	V7xx32x0xxxxG	DWG NO.		8V70104	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance
		Chen Bo 08/10`13	Chen Bo 08/08`13		X. ±0.5 X.X ±0.3 X.XX ±0.1 X° ±1°
SHEET: 01/01		UNIT: mm		SCALE: NONE	
				REV.: F	