






△ N = Number of poles

DimL=N×5.00+1.5
DimB=(N-1)×5.00

POLES	Dim L	Dim B
1p	±0.1	±0.15
2p-6p	±0.2	±0.15
7p-12p	±0.3	±0.25
13p-18p	±0.4	±0.35
19p-24p	±0.45	±0.4

- Material**
- Item ① Insulator body: Thermoplastic (UL 94V-0)
 - Item ② Insulating cover :Thermoplastic (UL94V-0)
 - Item ③ Contact pin : Brass,Tin plated
 - Item ④ Wire guard: Stainless steel

Electrical: cULus

● Voltage rating: 250V

● Current rating: 8A

● Wire range:

● Solid wire(AWG): 12-28

● Stranded wire(AWG): 12-28

● Wire strip length: 8-9mm

● Withstanding Voltage: 1.5KV

● Operating temperature: -40°C to +115°C

● Safety Approval: cULus

● Critical dimension: △

HM XX 50 x 1 xxxx G

No. OF POLES
01: 1 POLES
02: 2 POLES
24: 24 POLES

△ COL OR
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7004/P)
9 White(RAL1102)
C Multiple colors

0000 Standard @ Logo
000A Standard ANY Logo
Any special item by customer request,
please contact sales department.

RoHS compliant (lead<4%)
In copper Alloy

SIGN	DATE	DESCRIPTION	APPROVER
△	1/31/07	The soldering temperature from 245° to 250°	Aaron
△	05/28/13	change the structure	Da cheng
△	05/28/13	update the drawing	Da cheng
△			
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	HM 5.08mm Series Press fit Type			DWG NO.	8HM1012	Tolerance
PART NO.	HMxx50x1xxxxG			CUST NO.		X: ±0.50 X.X: ±0.30 X.XX: ±0.10 X°: ±1°
APPROVED	CHECKED	DESIGNED	DRAWN	SHEET: 01/01	REV: D	
	Da cheng 2013.05.28	Da cheng 2013.05.28				