

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20



© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.



| LOC | DIST | REVISIONS |     |                 |           |     |      |
|-----|------|-----------|-----|-----------------|-----------|-----|------|
|     |      | P         | LTR | DESCRIPTION     | DATE      | DWN | APVD |
| ES  | 00   |           | A   | INITIAL RELEASE | 06DEC2017 | AJ  | SH   |
|     |      |           |     |                 |           |     |      |
|     |      |           |     |                 |           |     |      |
|     |      |           |     |                 |           |     |      |
|     |      |           |     |                 |           |     |      |

D



C

B





- 1 MATES WITH XFP-MSA COMPLIANT TRANSCEIVERS.
- 2 DATUM **-X-** AND **-Y-** ESTABLISHED BY CUSTOMER.
- 3 DATUM **-A-** IS TOP SURFACE OF HOST BOARD.
- 4 INDICATED SURFACES TO BE CONDUCTIVE AND CONNECTED TO CHASSIS GROUND.
5. SEE COMPONENT DRAWINGS FOR COMPONENT DIMENSIONS AND INFORMATION.

|       |                          |                              |                          |             |                |
|-------|--------------------------|------------------------------|--------------------------|-------------|----------------|
| 22.9  | 1542706-3                | 1489948-2                    | 2303074-1                | NET WORKING | 2303075-3      |
| 15.8  | 1542618-2                | 1489948-2                    | 2303074-1                | SAN         | 2303075-2      |
| 13.6  | 1542656-4                | 1489948-2                    | 2303074-1                | PCI         | 2303075-1      |
| A MAX | HEAT SINK<br>PART NUMBER | HEATSINK CLIP<br>PART NUMBER | CAGE ASSY<br>PART NUMBER | APPLICATION | PART<br>NUMBER |

|                                                                                                                                   |  |                                                           |                                                                         |                        |                    |
|-----------------------------------------------------------------------------------------------------------------------------------|--|-----------------------------------------------------------|-------------------------------------------------------------------------|------------------------|--------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                                                            |  | DWN<br>18APR2016<br>CHK<br>18APR2016<br>APVD<br>18APR2016 | TE Connectivity                                                         |                        |                    |
| DIMENSIONS:<br>mm                                                                                                                 |  | PRODUCT SPEC<br>108-2127                                  | NAME<br>XFP CAGE ASSEMBLY<br>FRONT EMI SPRING W HEAT SINK<br>10 GIGABIT |                        |                    |
| TOLERANCES UNLESS OTHERWISE SPECIFIED:<br>0 PLC ±.1<br>1 PLC ±.01<br>2 PLC ±.001<br>3 PLC ±.0001<br>4 PLC ANGLES ±.0001<br>FINISH |  | APPLICATION SPEC<br>114-13096                             | SIZE<br>A200779                                                         | CAGE CODE<br>C-2303075 | RESTRICTED TO<br>- |
| MATERIAL<br>-                                                                                                                     |  | WEIGHT<br>-                                               | CUSTOMER DRAWING                                                        |                        |                    |
|                                                                                                                                   |  | SCALE<br>4:1                                              | SHEET<br>1                                                              | OF<br>3                | REV<br>A           |

A





DETAILED HOST BOARD MECHANICAL LAYOUT

|                                                                                                                                                      |  |                                                              |                                                                         |                        |
|------------------------------------------------------------------------------------------------------------------------------------------------------|--|--------------------------------------------------------------|-------------------------------------------------------------------------|------------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                                                                               |  | DWN 18APR2016<br>CHK 18APR2016<br>APVD 18APR2016<br>SEAN HAN | <b>TE</b> TE Connectivity                                               |                        |
| DIMENSIONS:<br>mm                                                                                                                                    |  | PRODUCT SPEC<br>108-2127                                     | NAME<br>XFP CAGE ASSEMBLY<br>FRONT EMI SPRING W HEAT SINK<br>10 GIGABIT |                        |
| TOLERANCES UNLESS OTHERWISE SPECIFIED:<br>0 PLC $\pm .1$<br>1 PLC $\pm .01$<br>2 PLC $\pm .001$<br>3 PLC $\pm .0001$<br>4 PLC ANGLES $\pm$<br>FINISH |  | APPLICATION SPEC<br>114-13096                                | RESTRICTED TO<br>-                                                      |                        |
| MATERIAL<br>-                                                                                                                                        |  | WEIGHT<br>-                                                  | SIZE<br>A200779                                                         | CAGE CODE<br>C-2303075 |
| CUSTOMER DRAWING                                                                                                                                     |  | SCALE<br>1:1                                                 | SHEET<br>3                                                              | OF<br>3                |
|                                                                                                                                                      |  |                                                              | REV<br>A                                                                |                        |