



△ Material

- Item ① Terminal housing: Thermoplastic (UL94V-0)
- Item ② Solder Pin: Brass Tin plated.
- Item ③ Spring clamp : Stainless steel
- Item ④ Terminal Cover : Thermoplastic (UL94V-0)

Electrical: CULUS

- Voltage rating: 300 V
- Current rating: 15A
- Wire range:
- Solid wire(AWG): 14-28
- Stranded wire(AWG): 14-28
- Wire strip length: 6-7 mm
- Withstanding Voltage: 16KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: **CE** **RoHS**
- Critical dimension: ∇

HHXX00X0XXXXG

△ No. OF POLES △ Color △ RoHS compliant (lead<4%)
 02 2 POLES 0 Black (RAL9005) In copper Alloy
 03 3 POLES 2 Red (RAL3001/D)
 ... 3 Orange(RAL2011/P)
 24 24 POLES 4 Yellow(RAL1018/A)
 ... 5 Green(RAL6018/T)
 ... 6 Blue (RAL5015/A)
 ... 8 Grey(RAL7004/P)
 ... 9 White(RAL1102)
 △ Multiple colors

0000 Standard @ Logo
 000A Standard ANY Logo
 Any special item by customer request, please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR, PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

△ N=NUMBER OF POLES

Dim L	N×5.0±0.9
Dim B	(N-1)×5.0

POLES	Dim L	Dim B
2p-6p	±0.2	±0.15
7p-12p	±0.3	±0.25
13p-18p	±0.4	±0.35
19p-24p	±0.45	±0.4

TITLE		HH - 5.0mm Series	
PART NO.	HHxx00xxxxxG	DWG NO.	8HH001
APPROVED	CHECKED	DESIGNED	DRAWN
	Da cheng	2013.07.04	Da cheng
	2013.07.04	2013.07.04	
CUST NO.		UNIT:	mm
		SCALE:	NONE
SHEET: 01/01		REV:	E
		Tolerance	X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°

SIGN	DATE	DESCRIPTION	APPROVER
△	07/04'13	update the drawing	Da cheng
△			

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!