





N = Number of poles
Dim A = N x 5.08 + 0.5
Dim B = (N - 1) x 5.08

	Dim A	Dim B
2-6p	±0.15	±0.15
7-12p	±0.20	±0.20
13-18p	±0.30	±0.30
19-24p	±0.40	±0.40

SIGN	DATE	DESCRIPTION	APPROVER
△	11.01'05	Standard spec is changed.	Marivn
△	8/07'06	Added VDE and TUV standard	梁仁松
△	12/02'08	With flange screw changed from "-" slot type to "+/-" slot type	Jacke
△	12/02'08	The temperature changed from -30°C, +105°C to -40°C, +115°C	Jacke
△	12/02'08	Add the tolerance table	Jacke
△	2010.03.12	Add the 2p mark	Jacke
△	2010.08.16	The design is changed	Chen Bo

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Item ① Clamp: Brass(CuZn), Ni plating
- Item ② Terminal screw: Steel Cr3+ Zinc plating "-" slot type
- Item ③ Female contact: PhBz, Tin plated
- Item ④ Terminal up body: Thermoplastic (UL94V-0)
- Item ⑤ Terminal down body: Thermoplastic (UL94V-0)
- Item ⑥ With flange screw: Steel Zinc plating M2.5 "+/-" slot type

△△ Electrical cULus/VDE/TUV

- Voltage rating: 300VAC/300VAC/300VAC
- Current rating: 15A/17A/15A
- Wire range: 2.5mm / 0.34-2.5mm²
- Solid wire(AWG): 12-24
- Stranded wire(AWG): 12-24
- Torque: 3.5Lb-In./0.5Nm/0.4Nm
- Screw: M3
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV/2.5KV/2.5KV
- Operating temperature: -40°C to +115°C
- Safety approval: cULus VDE TUV

TS xx 51 x C xxxx G

02 2 CONTACTS
03 3 CONTACTS
...
24 24 CONTACTS

Color

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)

RoHS

Pb<40,000ppm

0000: "@" Logo
000A: "ANYTEK" Mark
0091: "ANYTEK" Mark
Any special item by customer request.
please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	TS-5.08mm Series(W/latching hooks on the wire entry side) with flange								
PART NO.	TSxx51xCxxxxG			DWG NO.	8TS0103				
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance		
			Chen Bo 2010.08.16		UNIT: mm		X. ±0.50		
					SCALE: NONE		X.X ±0.30		
					SHEET: 01/01		X.XX ±0.10		
						REV.: H	X° ±1°		