

T1M-07-F-SV-L

T1M-05-F-SH-L



ISS1-10-L



CC09R-01-GF

(1.00 mm) .0394"

ISS1, CC09R, CC09M, T1M SERIES

DISCRETE WIRE COMPONENTS & TOOLING

SPECIFICATIONS

For complete specifications see www.samtec.com?ISS1, www.samtec.com?CC09R or www.samtec.com?CC09M

TOOLING

- Hand tool:
CAT-HT-309-2830-12
- Clamp for mounting hand tool to work table:
CAT-HT-MNT-01
- Mini Applicator:
CAT-MA-309-2830-XX-01

TYPE

NO. OF POSITIONS



LATCH

ISS1
= Single Row Body



-02, -03, -05, -07, -10, -15, -20

(Leave blank for no latch)

-L
= Positive Latch



LATCH



NO LATCH

Insulator Material:
Natural Nylon

TYPE

01


PLATING

CC09R
= Contact, Full Reel
(30,000 Parts per Reel)

CC09M
= Contact, Mini Reel
(5,000 Parts per Reel)

-GF
= 3 μ" (0.07 μm)
Gold contact
and tail

-T
= Tin



Contact Material:
Phosphor Bronze

Mates with:
S1SS(T)

SPECIFICATIONS

For complete specifications see www.samtec.com?T1M

Insulator Material:

Natural LCP

Terminal Material:

Phosphor Bronze

Weld Tab:

Phosphor Bronze

Plating:

Au or Sn over

50 μ" (1.27 μm) Ni

Operating Temp Range:

-55 °C to +85 °C

Current Rating:

3.3 A per pin

(1 pin powered)

Voltage Rating:

250 VAC/353 VDC

RoHS Compliant:

Yes

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



Note: Some lengths, styles and options are non-standard, non-returnable.

T1M

NO. OF POSITIONS

PLATING OPTION

ROW OPTION

LATCH

OPTION

-02, -03, -05, -07, -10, -15, -20

-F
= 3 μ" (0.07 μm)
Gold on contact,
Matte Tin on tail

-T
= Tin



-SH
= Single Row
Horizontal

-SV
= Single Row
Vertical




(Required in callout)
-L
= Positive Latch

-K
= (4.00 mm) .157" DIA
Polyimide Film Pick
& Place Pad
(-SH only)

-P
= Pick & Place Pad
(-SV only)



-SH



-SV

OTHER SOLUTIONS

- Without latch
Contact Samtec.