







N = Number of poles

Dim A=Nx5.08

Dim B=(N-1)x5.08

	Dim A	Dim B
2-6p	±0.20	±0.20
7-12p	±0.25	±0.25
13-18p	±0.30	±0.30
19-24p	±0.40	±0.40

SIGN	DATE	DESCRIPTION	APPROVER
△	02/07'06	Part No. changed	Tony
△	2010.03.23	Add the 2p mark	Jacke
△	2012.06.05	Update drawing	Chen Bo

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Item a Clamp: Steel zinc plated.
- Item b Terminal screw: Steel Zinc plating "-" slot type
- Item c Female contact: PhBz Tin plated
- Item d Terminal (Up body): Thermoplastic (UL94V-0)
- Item e Terminal (Down body): Thermoplastic (UL94V-0)
- Item f Clampage: Steel Zinc plated

Electrical cULus/TUV

- Voltage rating: 300VAC/300VAC
- Current rating: 20A/20A
- Wire range: 0.34-2.5mm²
- Solid wire(AWG): 12-22
- Stranded wire(AWG): 12-22
- Torque: 3.5Lb-In / 0.4Nm
- Screw: M2.5
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV/2.5KV
- Operating temperature: -40°C to +115°C
- Safety approval: cULus TUV
- Critical dimension: ∇

VM xx 5 5 x 0 xxxx G

Solid Block
02 2 CONTACTS
03 3 CONTACTS
...
24 24 CONTACTS

Color

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)
- C Green(RAL6018/U)

G RoHS compliant
(lead<4%)
In copper Alloy
0000: Standard
000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		VM 5.08mm W/O Flange Series				
PART NO.		VMxx55x0xxxxG		DWG NO.	8VM0101	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance
		Chen Bo 06/05`12	Chen Bo 06/05`12		UNIT: mm SCALE: NONE	X. ±0.50
				SHEET: 01/01	REV.: F	X.X ±0.30
						X.XX ±0.10
						X° ±1°