



SKI Series

SKI




Switching Operation

1 NC / 1 NO Contacts


Slow Action

601.6819.052
SKI-U1Z M3




High Activation Force

601.6819.139
SKI-U1Z FI50 M3



Radius Activation

601.6819.123
SKI-U1Z MRU




1 NC Contacts




2 NC Contacts

601.6869.056
SKI-A2Z M3




-

601.6869.122
SKI-A2Z MRU




2 NC / 1 NO Contacts Overlapping


601.6869.058
SKI-UV15Z M3



601.6869.145
SKI-UV15Z FI50 M3



601.6869.131
SKI-UV15Z MRU



Technical Information

	Slow Action	High Activation Force	Radius Activation
Maximum Switching Voltage	240V	240V	240V
Max. Switching Amps (up to)*	10A	10A	10A
B10d (up to)*	20 Million	20 Million	20 Million
Mechanical Service Life (up to)*	10 x 10 ⁶	10 x 10 ⁵	10 x 10 ⁶
Switching Frequency	≤ 30/min	≤ 30/min	≤ 30/min
Operating Temperature	-30 °C to +80 °C	-30 °C to +80 °C	-30 °C to +80 °C
Protection Rating	IP65	IP65	IP65
Utilization Category (up to)*	AC-15, Ue/Ue 240V 3A	AC-15, Ue/Ue 240V 3A	AC-15, Ue/Ue 240V 3A
Rate Insulation Voltage	250VAC	250VAC	250VAC


Approvals

* Depending on switching system - see technical information for details




Replacement actuator keys:


M3 ACTUATOR KEY
311.2850.340



M2 ACTUATOR KEY
311.2850.345



MRU ACTUATOR KEY
391.1452.058



Drawing dimensions in mm