







5
 N = Number of poles
 Dim L = N x 9.5 + 1.5
 Dim P = (N - 1) x 9.5

Poles	Tol.	Dim L & P
2-4p		±0.20
5-8p		±0.25
9-16p		±0.35
17-23p		±0.40
24-30p		±0.50



PCB Layout

SIGN	DATE	DESCRIPTION	APPROVER
△	10/20'08	Add APPROVAL: : CQC	Kind
△	4/17'09	Explanation changed	Eris
△	06/15'11	Critical dimension is changed.	Tason
△	06/15'11	The Wire Range is changed from 20-14AWG to 22-14AWG	Tason
△	06/15'11	The tolerance table is changed.	Tason
△	06/16'11	The dimension is changed from (5.6) to (5.5)	Tason
△	11/10'12	Change the screw plating specification	Jacky
△	12/23'13	Change the withstand voltage, current, Screw Torque.	Guoxue

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

MATERIALS ELECTRICAL	cULus	CQC
△ RATED VOLTAGE & CURRENT:	300 V, 30A	/ 300V 24A △
WITHSTAND VOLTAGE:	AC2500V/min △	
INSULATION RESISTANCE:	1000 MΩ OR MORE AT DC 500 V	
OPERATING TEMPERATURE RANG:	-40 °C ~ +115 °C	
SCREW TORQUE VALUE:	10.54 Lb-In.	/ 0.8Nm △
△ WIRE RANGE:	22 - 10 AWG	/ 22-14 AWG △
1) MOLDED PARTS:	Thermoplastic, UL 94 V-0 BLACK	
2) TERMINAL:	BRASS, 0.8t, Tin PLATED	
3) TERMINAL SCREWS:	STEEL, M3.5	

△ Critical dimension:
△ APPROVAL:

PART NO.:

YK 442 xx 0 x x 00G

NO. OF POLES

02: 2 POLES
 03: 3 POLES
 04: 4 POLES
 ...
 30: 30 POLES

TERMINAL & SCREW PLATED 0: "0" MARK

△ 0: TERMINAL & SCREW: G/F 1: "ANY" MARK
△ 1: TERMINAL: G/F, SCREW: Zinc
△ 2: TERMINAL: Sn, SCREW: G/F
△ 3: TERMINAL: Sn, SCREW: Zinc

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		YK-442 Series								
PART NO.		YK442xx0xx00G				DWG NO.	8YK0001-442			
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.				Tolerance	
			Guoxue 2014.01.08	Guoxue 2014.01.08			UNIT: mm		X.	±0.50
							SCALE: NONE		X.X	±0.30
					SHEET: 01/01		REV.: I		X.XX	±0.10
									X°	±1°

SHEET: 01/01

REV.: 1