




SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

- Material:
- Item ① Insulator(housing): Thermoplastic (UL94V-0)
  - Item ② Spring clamp: Stainless steel
  - Item ③ Terminal Body(contact pin): Brass.
  - Item ④ Insulator(Cover): Thermoplastic (UL94V-0)

- Electrical: cULus
- Voltage rating: 300V
  - Current rating: 10A
  - Wire range:
  - Solid wire(AWG): 12-28
  - Stranded wire(AWG): 12-28
  - Wire strip length: 8-9mm
  - Withstanding Voltage: 1.6KV
  - Operating temperature: -40°C to +115°C
  - Soldering temperature: 250°C±10°C/5 Sec
  - Safety Approval: 



H3 xx 2 0 x 0 xxxx G


- No. OF POLES
- 02: 2 POLES
  - ...
  - 12: 12 POLES
- COLOR
- 0: BLACK
  - 5: GREEN
  - 6: BLUE
  - 8: GREY

G: Pb<40000ppm

0000: Standard

Any special item by customer request. please contact sales department.

POLE	2	3	4	5	6	7	8	9	10	11	12
A	16.50	26.50	36.50	46.50	56.50	66.50	76.50	86.50	96.50	106.50	116.50
B	10.00	20.00	30.00	40.00	50.00	60.00	70.00	80.00	90.00	100.00	110.00
Tol.	±0.25						±0.40				

<b>ANYTEK</b>				<b>CUSTOMER COPY</b>			
ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD							
TITLE		H3 10.0mm Series					
PART NO.		H3xx20x0xxxxG			DWG NO.		8H30003
APPROVED		DESIGNED	DRAWN	CUST NO.		Tolerance	
		Tony	Tony			X. ±0.50	
		2008.05.29	2008.05.29			X.X ±0.30	
						X.XX ±0.10	
				SHEET: 01/01		X° ±1°	
				UNIT: mm			
				SCALE: NONE			
				REV.: B			