

INTERCONNECTS

SERIES 800 & 801 • 2,54 GRID (0,76 DIA. PINS), STRAIGHT & RIGHT ANGLE HEADERS AND SOCKETS • SINGLE ROW STRIPS




FIG. 1




FIG. 2




FIG. 3





FIG. 4

- Pin interconnects available with straight MM #7007 or right angle MM #5005 solder tails. See page 215 for details
- Sockets are available with straight MM #1304 or right angle MM #1305 soldertails. See pages 177 and 179 for details
- MM #1304 and MM #1305 receptacles use Hi-Rel, 6-finger BeCu #47 contact rated at 4.5 amps. Receptacles accept 0,76 diameter and 0,64 square pins. See page 256 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations



ORDERING INFORMATION

FIG. 1	Series 800...10-001		Straight Pin Header		
	800-XX-0-10-001000 Specify number of pins 01-64				
FIG. 2	Series 800...20-001		Right Angle Pin Header		
	800-XX-0-20-001000 Specify number of pins 02-64				
RoHS-2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Enviromental Data, See page 264					
SPECIFY PLATING CODE XX=		10 	90	40 	
Pin Plating 		0,25µm Au	5,08µm Sn/Pb	5,08µm Sn	

FIG. 3	Series 801...10-001	Straight Socket					
	801-XX-0	-10-001000	01-50				
	Specify number of pins						
FIG. 4	Series 801...20-001	Right Angle Socket					
	801-XX-0	-20-001000	01-50				
	Specify number of pins						
RoHS-2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Enviromental Data, See page 264							
SPECIFY PLATING CODE XX=							
Sleeve (Pin)	91	93	99	41	43	44	47
Contact (Clip)	0,25µm Au	0,76µm Au	2,54µm Sn/Pb	0,25µm Au	0,76µm Au	2,54µm Sn	Au Flash

★ 44 Plating Non-Standard

