

## SUMMARY

### # Wires

|             |   |
|-------------|---|
| Low voltage | 1 |
|-------------|---|



*Image is for illustrative purpose only*

|                  |                |
|------------------|----------------|
| Series           | 00             |
| Termination type | Male crimp     |
| IP rating        | 50             |
| AWG wire size    | 0.00 - 0.00    |
| Cable Ø          | 0.00 - 3.00 mm |
| Status           | active         |

### Download

[Request a quote](#)

[Catalog](#)

## TECHNICAL DETAILS

### Mechanics

|                   |   |
|-------------------|---|
| Shell Style/Model | FFS*: Straight plug with cable crimping   |
| Keying            | Circular, male  |
| Housing Material  | Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Weight            | 3.29 g  |

### Performance

|               |                        |
|---------------|------------------------|
| Configuration | 00.113 : 1 Low Voltage |
| Insulator     | T: PTFE                |
| Rated Current | 8 Amps                 |

### Specifications


Vtest: 850 V (AC), 1200 V (DC)

### Others

Salt Spray Corrosion: >1000 hr

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# DRAWINGS



## Dimensions

|     | A    | L    | M    |
|-----|------|------|------|
| mm. | 6.4  | 31   | 23   |
| in. | 0,25 | 1,22 | 0,91 |

# RECOMMENDED BY LEMO

## Tools

Spanner wrench: [DCP.99.055.TC](#)

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.