




RECOMMENDED PCB LAYOUT

DIM		TOL			
		2--6P	7--12P	13--18P	19--24P
Dim L	(N-1)×5.0+7.0	±0.15	±0.25	±0.35	±0.40
Dim B	(N-1)×5.0	±0.15	±0.25	±0.35	±0.40

SIGN	DATE	DESCRIPTION	APPROVER
△	1/29/07	Dim. L changed	Tony
△	1/29/07	Soldering temperature changed from 245° to 250°	Tony
△	8/01/08	Operating temperature changed	Marvin
△			

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item ③ Short male contact pin: Copper Tin plated
- Item ④ long male contact pin: Copper Tin plated
- Item ⑤ Terminal(housing): Thermoplastic (UL94V-0)
Electrical: cULus
- Voltage rating: 300V
- Current rating: 20A
- Withstanding Voltage: 1.6 KV
- ⚠ ● Operating temperature: -40°C to +115°C
- ⚠ ● Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval:  us

VL xx 7 1 x 1 xxxx G

No. OF POLES —

04: 2x2 POLES

48: 2x24 POLES

COLOR

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)

— G: Pb<40000ppm

— 0000: "@ " Logo

000A: "ANYTEK" Mark

Any special item by
customer request.
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		VL-5.0mm Right-angle Series						
PART NO.		VLxx71x1xxxxG		DWG NO.		8VL0201		
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance	
	Marvin 2008.08.01	Marvin 2008.08.01	Marvin 2008.08.01		UNIT: mm		X.	±0.50
					SCALE: NONE		X.X	±0.30
					SHEET: 01/01 REV: E		X.XX	±0.10
							X°	±1°