







△ N=Number of Poles
Dim.P=(N-1)×5.0
Dim.L=N×5.0+1.0

Poles Dim.	1P	2P-6P	7P-12P	12P-18P	19P-24P
Dim.L	±0.10	±0.20	±0.25	±0.30	±0.40
Dim.P		±0.15	±0.20	±0.25	±0.35

△ PCB LAYOUT
Bottom view

SIGN	DATE	DESCRIPTION	APPROVER
△	10/30'09	The dimension changed from 19.1 to 19.1±0.50	Kind
△	10/30'09	Add tolerance table for Dim.L and Dim.P	Kind
△	10/30'09	Terminal lever material changed to thermoplastic (UL94-HB)	Kind
△	04/23'13	Update the drawing	Da cheng

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Item 1 Solder pin : Brass , Tin plated
- Item 2 Spring clamp : Stainless steel
- Item 3 Terminal housing: Thermoplastic (UL94V-0)
- Item 4 Terminal cover: Thermoplastic (UL94V-0)
- △ ● Item 5 Terminal lever: Thermoplastic (UL94V-HB)

Electrical

- Voltage rating: 300V
- Current rating: 15A
- Wire range:
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- △ ● Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: cULus
- △ ● Critical dimension: △

HT xx 00 x 0 xxxx G

- △ 01 1 CONTACTS
02 2 CONTACTS
...
24 24 CONTACTS

- △ Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7004/P)
9 White(RAL1102)
C Multiple colors

- △ G: RoHs compliant
(lead<4%)
In copper Alloy
000 0 Standard @ Logo
000 A Standard ANY Logo
009 1 Standard ANY Logo
Any special item by
customer request,
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		HT-5.0 Series			
PART NO.	HTxx00x0xxxxG			DWG NO.	8HT0001
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Da cheng 2013.04.23	Da cheng 2013.04.23		
		SHEET: 01/01		UNIT: mm	X. ±0.50
				SCALE: NONE	X.X ±0.30
				REV.: F	X.XX ±0.10
					X° ±1°