

SIGN	DATE	DESCRIPTION	APPROVER
△	07/02'11	No. OF POLES is changed	Runner
△	09/24'11	Add is "cULus" mark	Runner
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item ① Insulator(Cover): Thermoplastic (UL94V-0)
- Item ② Insulator(housing): Thermoplastic (UL94V-0)
- Item ③ Spring clamp: Stainless steel
- Item ④ Contact pin (fourth level): Brass, Tin plated
- Item ⑤ Contact pin (third level): Brass, Tin plated
- Item ⑥ Contact pin (second level): Brass, Tin plated
- Item ⑦ Contact pin (first level): Brass, Tin plated

Electrical: cULus

- Voltage rating: 300V
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec



- △ ● Safety Approval: 
- Critical dimension: 

HS xx 30 x 0 xxxx G

No. OF POLES  G: Pb<40000ppm

- △ 08: 4×2 POLES
- 92: 4×23 POLES
- 96: 4×24 POLES
- COLOR  0000: "@" Logo (Standard)
- 000A: "ANYTEK" Mark
- Any special item by customer request. please contact sales department.

0: BLACK
5: GREEN (RAL 6018/T)
6: BLUE
8: GREY (RAL 7004/P)



PCB Layout

N = Number of poles.

Dim.A = N×5.08+1.0

Dim.B = (N-1)×5.08

POLE	4×2 ~ 4×6	4×7 ~ 4×12	4×13 ~ 4×18	4×19 ~ 4×24
Dim.A	±0.15	±0.25	±0.35	±0.45
Dim.B	±0.15	±0.25	±0.30	±0.40

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		HS 5.08mm Series (Solder pins in line)					
PART NO.		HSxx30x0xxxxG			DWG NO. 8HS0001		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance		
		Runner 2011.09.24	Tony 2007.12.19		UNIT: mm	X. ±0.50	
						X.X ±0.30	
				SHEET: 01/01	SCALE: NONE	X.XX ±0.10	
						X° ±1°	