




SIGN	DATE	DESCRIPTION	APPROVER
⚠	01/27/07	The Soldering temperature from 245° to 250°	Aaron
⚠	01/27/07	Add "VDE" stipulation	Aaron
⚠	8/6/07	The body bottom is changed.	Marvin
⚠	06/05/13	change the electrical specification	Da cheng
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item 1 Insulating body :Thermoplastic (UL94V-0)
- Item 2 Insulating lever :Thermoplastic (UL94V-0)
- Item 3 Contact pin : Brass, Tin plated
- Item 4 Spring clamp : Stainless steel

⚠⚠Electrical	cULus	TUV
● Voltage rating:	300V	500V
● Current rating:	8A	10A
● Wire range:	0.5-1.5mm ²	
● Solid wire(AWG):	16-20	
● Stranded wire(AWG):	16-20	
● Wire strip length:	8-9mm	
● Withstanding Voltage:	1.6KV	1.89KV
● Operating temperature:	-40°C to +115°C	
● Soldering temperature:	260°C±5°C/5 Sec	
⚠ Safety Approval:	cULus	TUV
⚠ Critical dimension:	▽	

HV xx 30 x 0 xxxx G

RoHs compliant (lead<4%) In copper Alloy

Poles: 02 2Contacts, 03 3Contacts, 24 24Contacts

Color: 8 Grey (RAL 7004/P), 9 Orange

0000 Standard @ Logo, 000A Standard ANY Logo

Any special item by customer request, please contact sales department.

N = Number of poles
Dim L=Nx3.81
Dim B=(N-1)x3.81

	Dim L	Dim B
2-6p	±0.15	
7-12p	±0.20	
13-18p	±0.25	
19-24p	±0.30	

ANYTEK

CUSTOMER COPY
ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	HV-3.81mm Series				
PART NO.	HVxx30x0xxxxG		DWG NO.	8HV0001	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance
		Da cheng 2013.06.05	Da cheng 2013.06.05		X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°
SHEET: 01/01			UNIT: mm SCALE: NONE REV.: G		