





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	19MAR2021	J.W	E.J
	A1	ECN-22-164503	14 JUL2022	J.G	Z.Z

D


C





B

A



- 1 MATERIAL: SEE TABLE LIST
- 2. WORKING TEMPERATURE RANGE: -40°C ~ +125°C(INCLUDING SELF-HEATING)
- 3. MINIMUM INSULATION RESISTANCE BETWEEN ADJACENT TERMINALS: 100MΩ AT DC500V .
- 4. NO DEFINED DIMENSIONS ACCORDING TO 3D MODEL.
- 5 THE SEALING CONTACT AREA ON COVER POLISHED, RECOMMAND ROUGHNESS Ra<1.6
- 6. RECOMMEND MOUNTING SCREW: M3XL(L=8MM+L1), L1=TICKNESS OF COVER
- 7. PLUG TE PART NUMBER: 4-1437290-0



							
CODING1 DOUBLE LOCK TE PART NUMBER: 2384723-1		CODING2 DOUBLE LOCK TE PART NUMBER: 2384723-2		CODING3 UPPER LOCK TE PART NUMBER: 2384723-3		CODING4 UPPER LOCK TE PART NUMBER: 2384723-4	
4	4	4	4	C3604	34P BUSHING (M3)	8	
1	1	1	1	PBT/PET	34P JOINTER	7	
9	9	9	9	COPPER ALLOY	34P PIN4	6	
8	8	8	8	COPPER ALLOY	34P PIN3	5	
8	8	8	8	COPPER ALLOY	34P PIN2	4	
9	9	9	9	COPPER ALLOY	34P PIN1	3	
1	1	1	1	SILICON	34P SEAL	2	
1				PBT/PET	34P HOUSING UPPER LOCK CODING2	1	
	1				34P HOUSING UPPER LOCK CODING1		
		1			34P HOUSING DOUBLE LOCK CODING2		
			1		34P HOUSING DOUBLE LOCK CODING1		
2384723-4	2384723-3	2384723-2	2384723-1	MATERIAL	DESCRIPTION	ITEM	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±0.1
2 PLC ±0.01
3 PLC ±0.001
4 PLC ±0.0001
ANGLES ±
FINISH -

MATERIAL

1

DWN J.WANG 19MAR2021
CHK R.CHEN 19MAR2021
APVD F.JIANG 19MAR2021

PRODUCT SPEC
108-78140
APPLICATION SPEC
-
WEIGHT
-

CUSTOMER DRAWING

NAME
SUPERSEAL 34P HEADER 90 DEGREE

SIZE A2
CAGE CODE 00779
DRAWING NO C-2384723
RESTRICTED TO
-
SCALE 2:1
SHEET 1 OF 1
REV A1

1471-9 (3/13)