



Dimension


Dim A	Nx5.08
Dim B	(N-1)x5.08

N=Number of contacts

Poles	Dim A	Dim B
2-6p	±0.15	±0.15
7-12p	±0.25	±0.25
13-18p	±0.35	±0.35
19-24p	±0.40	±0.40



SECTION A-A



P.C.B Layout

SIGN	DATE	DESCRIPTION	APPROVER
△			
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item① Terminal screw: Steel Zinc plating "--" slot type
- Item② Clamp : Brass , Ni plating
- Item③ Wire guard solder pin : Brass,Tin plated
- Item④ Terminal housing : PA 66 (UL94V-0)

Electrical

- Voltage rating: 300VAC
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 12-24
- Stranded wire(AWG): 12-24
- Torque(Lb-In): 3.5
- Screw: M2.5
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec

PART NO.

YR xx 21 x 0 xxxx G				RoHS Pb<40,000ppm
Poles	0	Black (RAL9005)	0000	Standard @ Logo
02 2Contacts	2	Red (RAL3001/D)	000A	Standard ANY Logo
03 3Contacts	3	Orange(RAL2011/P)	Any special item by customer request, please contact sales department.	
— — —	4	Yellow(RAL1018/A)		
24 24Contacts	5	Green(RAL6018/T)		
	6	Blue (RAL5015/A)		
	8	Grey(RAL7035/D)		

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	YR 5.08 Series 2P-24P						
PART NO.	YRxx21x0xxxxG			DWG NO.	8YR0101		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance		
		Aaron 2010.05.18	Aaron 2010.05.18			UNIT: mm	X. ±0.50
						SCALE: NONE	X.X ±0.30
						REV.: B	X.XX ±0.10
					SHEET: 01/01		X° ±1°