



REVISIONS		
REV	DESCRIPTION	DATE
PA1	INITIAL RELEASE	2019-11-27
PA2	CHANGE THE SHELL PLATING AND EARTH PIN LENGTH	2019-12-13
PA3	CHANGE THE DIMENSIONS	2020-02-28
PA4	CHANGE THE PRODUCT CODE	2020-05-26



SPECIFICATIONS / 技术参数	
SERVER RATING 服务等级	A
NUMBER OF CONTACTS 端子数量	4
CONTACT SIZE 端子大小	#12
CURRENT RATE 额定电流	23A/PIN
OPERATING VOLTAGE 额定电压	500V AC 最大
OPERATING TEMPERATURE 工作温度	-55°C TO 125°C
D.W.V. 耐电压	2000V AC
INSULATION RESISTANCE 绝缘电阻	1000 M Ω 最小(AT 500VDC)
CONTACT RESISTANCE 端子接触电阻	5 m Ω 最大
DURABILITY 耐久性	100次
SALT SPRAY 盐雾	5%NaCl, 48小时
AIR LEAKAGE 气密性	2.9X10 ⁴ P α 压力下保持1分钟不泄露
SHELL PLATING 外壳电镀	BLACK ZINC PLATING 黑锌电镀
APPLICABLE WIRE 适用线规	3.5mm ² 最大

NOTES: 1. THE REFERENCED PRODUCT IS IN COMPLIANCE WITH THE MAXIMUM CONCENTRATION VALUES(MCVS) AS SET BY RoHS 2.0 DIRECTIVE 2011/65/EU AND ANNEX II AMENDMENT DIRECTIVE (EU)2015/863.

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND
SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR
ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES
WITHOUT WRITTEN PERMISSION FROM THE AMPHENOL CORP.


N/A


NEXT ASSEMBLY

PRO/ENGINEER INFORMATION	
Pro/e Model Used:	10-764272-10P.ASSEM
Drawing Name:	10-764272-10P

WHITE INK STAMP "AMPHENOL", ASSEMBLY NUMBER
AND DATE CODE APPROX.
白色油墨印字 AMPHENOL + 产品编号 + 制造日期(年周 1930)

白色油墨印字 AMPHENOL + 产品编号 + 制造日期(年周 1930)



7	1	RETAINING RING	COPPER ALLOY, TIN PLATING	
6	1	REAR INSULATOR	PLASTIC	COLOR: BLACK
5	1	EARTH PIN	COPPER ALLOY, NICKEL PLATING	
4	1	FRONT INSULATOR	RUBBER	COLOR: BLACK
3	1	CONTACT, EARTH	COPPER ALLOY, SILVER PLATING	CONTACT NO:D
2	3	#12 CONTACT	COPPER ALLOY, SILVER PLATING	CONTACT NO: A, B, C
1	1	SHELL	ALUMINUM ALLOY, ZINC PLATING	COLOR: BLACK
POS	QTY	DESCRIPTION	MATERIAL & FINISH	NOTE
PARTS LIST				
APPROVALS		DATE	AMPHENOL INDUSTRIAL OPERATIONS Amphenol Technology(Zhuhai)Co.,Ltd No.63, Xingnan Road, Sarciao Town, Jinwan, Zhuhai	
PREPARED BY	LIANG XU	May-26-20		
ENGINEER IN CHARGE	LIANG XU			
DESIGN MANAGER	RAN XIAO			
DESIGN ACTIVITY GROUP		C3	CONNECTOR, ELECTRICAL RECEPTACLE 97-3102E-18-10P(400)(946), GROUND-TYPE CONDUCTIVE BLACK ZINC PLATED	
THIRD ANGLE PROJECTION				
				
SIZE	CAGE CODE	DOCUMENT NO.		REV.
C	77820	10-764272-10P		PA4
SCALE: 2:0		REF. N/A		SHEET 1 OF 1