CONDUCTIVE POLYMER HYBRID ALUMINUM ELECTROLYTIC CAPACITORS


nichicon

GYB

Chip Type, 105°C High Reliability

For SMD | HR High Ripple Current | Z Low Impedance | L Long Life

- High Reliability, Low ESR,High ripple current.
- Long life of 10000 hours at 105°C.
- Compliant to the RoHS directive (2011/65/EU,(EU)2015/863).
- AEC-Q200 Qualified. Please contact us for details.




■Specifications

Item	Performance Characteristics
Category Temperature Range	−55 to +105°C
Rated Voltage Range	16 to 80V
Rated Capacitance Range	10 to 560μF
Capacitance Tolerance	±20% at 120Hz, 20°C
Tangent of loss angle (tan δ)	Rated voltage (V): 16 / 25 / 35 / 50 / 63 / 80 tan δ (max.): 0.16 / 0.14 / 0.12 / 0.10 / 0.08 / 0.08 120Hz 20°C
ESR	Less than or equal to the specified value at 100kHz, 20°C
Leakage Current ※	After 2 minutes' application of rated voltage at 20°C, leakage current is not more than 0.01CV(μA). 80V:After 2 minutes' application of rated voltage at 20°C, leakage current is not more than 0.05CV(μA).
Temperature Characteristics (Max.Impedance Ratio)	Z(−25°C) / Z(+20°C) ≦ 2 Z(−55°C) / Z(+20°C) ≦ 2.5 (100kHz)
Endurance	The specifications listed at right shall be met when the capacitors are restored to 20°C after D.C. bias plus rated ripple current is applied for 10000 hours at 105°C, the peak voltage shall not exceed the rated voltage. Capacitance change: Within ± 30% of initial capacitance value tan δ: 200% or less of the initial specified value ESR: 200% or less of the initial specified value Leakage current: Less than or equal to the initial specified value
Shelf Life	After storing the capacitors under no load at 105°C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the specified values for the endurance characteristics listed above.
Damp Heat (Steady State)	The specifications listed at right shall be met when the capacitors are restored to 20°C after the rated voltage is applied for 2000 hours at 85°C, 85% RH. Capacitance change: Within±30% of the initial capacitance value tan δ: 200% or less of the initial specified value Leakage current: Less than or equal to the initial specified value
Resistance to Soldering Heat	The capacitors are kept on a hot plate for 30 seconds, which is maintained at 250°C. The capacitors shall meet the characteristic requirements listed at right when they are removed from the plate and restored to 20°C. Capacitance change: Within±10% of the initial capacitance value tan δ: Less than or equal to the initial specified value Leakage current: Less than or equal to the initial specified value
Marking	Black print on the case top.


※ I : Leakage Current (μA), C : Rated Capacitance (μF), V : Rated Voltage (V)

■Dimensions


(φ6.3)【Standard】



(φ8, φ10)【Standard】



(φ6.3)【Vibration Resistance】



● Dimension table in next page.

Type numbering system (Example : 35V 47μF)

1	2	3	4	5	6	7	8	9	10	11	12	13	14
G	Y	B	1	V	4	7	0	M	C	Q	1	G	S

Taping code
Size code
Configuration
Capacitance tolerance (±20%)
Rated capacitance (47μF)
Rated voltage (35V)
Series name
Type

Size	Code
Standard	Q
Vibration Resistance	W

Standard (mm)

φD×L	6.3×5.8	6.3×7.7	8×10	10×10	10×12.5
A	7.3	7.3	9.0	11.0	11.0
B	6.6	6.6	8.3	10.3	10.3
C	6.6	6.6	8.3	10.3	10.3
E	2.2	2.2	3.1	4.5	4.5
L	5.8	7.7	10.3	10.3	12.5
H	0.5 to 0.8	0.5 to 0.8	0.8 to 1.1	0.8 to 1.1	0.8 to 1.1

Vibration Resistance (mm)

φD×L	6.3×7.7	8×10	10×10	10×12.5
A	7.3	9.0	11.0	11.0
B	6.6	8.3	10.3	10.3
C	6.6	8.3	10.3	10.3
E	2.2	3.1	4.5	4.5
L	7.7	10.5	10.5	12.8
H	0.5 to 0.8	1.1 to 1.5	1.1 to 1.5	1.1 to 1.5


Voltage

V	16	25	35	50	63	80
Code	C	E	V	H	J	K

● Frequency coefficient of rated ripple current

Frequency	120Hz	1kHz	10kHz	100kHz or more
Coefficient	0.15	0.40	0.75	1.00

(φ8, φ10)【Vibration Resistance】



CAT.8100N

GYB

■Dimensions

Rated Voltage (V) (code)	Rated Capacitance (μF)	Case Size φD×L (mm)	tan δ	Leakage Current (μA) (at 20℃ after 2 minutes)	ESR (mΩ) max. (20℃/100kHz)	Rated Ripple (mArms) (105℃/100kHz)	Part Number
16 (1C)	82	6.3×5.8	0.16	13.12	50	1400	GYB1C820MCQ1GS
	150	6.3×7.7	0.16	24.0	30	2100	GYB1C151MC□1GS
	270	8×10	0.16	43.2	25	2400	GYB1C271MC□1GS
	470	10×10	0.16	75.2	20	2600	GYB1C471MC□1GS
	560	**10×12.5**	**0.16**	**89.6**	**15**	**3500**	**GYB1C561MC□1GS**
25 (1E)	47	6.3×5.8	0.14	11.75	50	1300	GYB1E470MCQ1GS
	56	6.3×5.8	0.14	14.00	50	1300	GYB1E560MCQ1GS
	68	6.3×7.7	0.14	17.00	30	2000	GYB1E680MC□1GS
	100	6.3×7.7	0.14	25.00	30	2000	GYB1E101MC□1GS
	150	8×10	0.14	37.50	27	2300	GYB1E151MC□1GS
	220	8×10	0.14	55.00	27	2300	GYB1E221MC□1GS
	270	10×10	0.14	67.50	20	2500	GYB1E271MC□1GS
	330	10×10	0.14	82.50	20	2500	GYB1E331MC□1GS
	470	10×12.5	0.14	117.50	16	3500	GYB1E471MC□1GS
35 (1V)	33	6.3×5.8	0.12	11.55	60	1300	GYB1V330MCQ1GS
	47	6.3×5.8	0.12	16.45	60	1300	GYB1V470MCQ1GS
	68	6.3×7.7	0.12	23.80	35	2000	GYB1V680MC□1GS
	100	8×10	0.12	35.00	27	2300	GYB1V101MC□1GS
	150	8×10	0.12	52.50	27	2300	GYB1V151MC□1GS
	220	10×10	0.12	77.00	20	2500	GYB1V221MC□1GS
	270	10×10	0.12	94.50	20	2500	GYB1V271MC□1GS
	330	10×12.5	0.12	115.50	16	3500	GYB1V331MC□1GS
50 (1H)	22	6.3×5.8	0.10	11.00	80	1100	GYB1H220MCQ1GS
	33	6.3×7.7	0.10	16.50	40	1600	GYB1H330MC□1GS
	47	8×10	0.10	23.50	30	1800	GYB1H470MC□1GS
	68	8×10	0.10	34.00	30	1800	GYB1H680MC□1GS
	100	10×10	0.10	50.00	28	2000	GYB1H101MC□1GS
	120	10×10	0.10	60.00	28	2000	GYB1H121MC□1GS
	150	10×12.5	0.10	75.00	18	3200	GYB1H151MC□1GS
63 (1J)	10	6.3×5.8	0.08	6.30	120	1000	GYB1J100MCQ1GS
	22	6.3×7.7	0.08	13.86	80	1500	GYB1J220MC□1GS
	33	8×10	0.08	20.79	40	1600	GYB1J330MC□1GS
	47	8×10	0.08	29.61	40	1600	GYB1J470MC□1GS
	56	10×10	0.08	35.28	30	1800	GYB1J560MC□1GS
	68	10×10	0.08	42.84	30	1800	GYB1J680MC□1GS
	82	10×10	0.08	51.66	30	1800	GYB1J820MC□1GS
	100	10×12.5	0.08	63.00	20	3000	GYB1J101MC□1GS
80 (1K)	**22**	**8×10**	**0.08**	**88.0**	**45**	**1300**	**GYB1K220MC□1GS**
	33	**10×10**	**0.08**	**132.0**	**36**	**1600**	**GYB1K330MC□1GS**
	47	**10×10**	**0.08**	**188.0**	**36**	**1600**	**GYB1K470MC□1GS**
	56	**10×12.5**	**0.08**	**224.0**	**26**	**2800**	**GYB1K560MC□1GS**

□ : Enter the appropriate configuration code.

Blue : New product (as of October 2024)

- For taping specifications, recommended land size/soldering by reflow and minimum order quantity, please refer to the Guidelines for Aluminum Electrolytic Capacitors.