






N = Number of poles.
Dim.A = $N \times 5.0 + 1.0$
Dim.B = $(N-1) \times 5.0$

POLE	$4 \times 2 \sim 4 \times 6$	$4 \times 7 \sim 4 \times 12$	$4 \times 13 \sim 4 \times 18$	$4 \times 19 \sim 4 \times 24$
Dim.A	± 0.15	± 0.25	± 0.35	± 0.45
Dim.B	$+0.15$	$+0.25$	$+0.30$	$+0.40$

— G: Pb<40000ppm
— 0000: “@” Logo (Standard)
000A: “ANYTEK” Mark
Any special item by
customer request.
please contact sales
department.

ANYTEK				CUSTOMER COPY ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD				
TITLE		HS 5.0mm Series (Solder pins in line)						
PART NO.		HSxx00x0xxxxG			DWG NO.		8HS0101	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance	
			Runner 2011.09.24	Kind 2009.6.8			UNIT: mm	X. ±0.50
							SCALE: NONE	X.X ±0.30
					SHEET: 01/01		REV: D	X.XX ±0.10
								X° ±1°