







N = Number of poles

Dim L = N x 5.0

Dim P = (N - 1) x 5.0

Dim B = N x 5.0 + 1.5

	Dim L	Dim P	Dim B
2-6p	±0.20	±0.20	±0.20
7-12p	±0.25	±0.25	±0.25
13-18p	±0.30	±0.30	±0.30
19-24p	±0.40	±0.40	±0.40



P.C.B LAYOUT

SIGN	DATE	DESCRIPTION	APPROVER
△	2011.07.13	DWG NO is changed from 8T40301 to 8T40501	Chen Bo
△	2011.07.13	Add the tolerance table	Chen Bo

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material

- Item 1 Terminal housing Thermoplastic (UL94V-0)
- Item 2 Terminal screw Steel Zinc plating "+/-" slot type
- Item 3 Terminal body Brass stamping clamp, Tin plated
- Item 4 Wire guard Stainless steel

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 12-20
- Stranded wire(AWG): 11-20
- Torque(Lb-In): 3.5
- Screw: M3
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C ± 10°C / 5 Sec
- Safety Approval Data:
- Critical dimension:

T4 xx 04 x x xxxx G

- Solid block → RoHS
Pb < 40,000ppm
- 02 2 CONTACTS
03 3 CONTACTS
...
24 24 CONTACTS
- DIM C Length
2 4.4mm
(Connector though type)
3 3.0mm
(Connector though type)
- Color →
0 Black (RAL9005)
5 Green (RAL6018/T)
6 Blue (RAL5015/A)
8 Grey (RAL7035/P)
- 0000 Standard @ Logo
000A Standard ANY Logo
Any special item by customer request, please contact sales department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	T4-5.0mm Solid block Connector though type				
PART NO.	T4xx04xxxxxxG		DWG NO.	8T40501 △	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance
			Chen Bo 2011.07.13		X. ±0.50
					X.X ±0.30
					X.XX ±0.10
					X° ±1°

UNIT: mm

SCALE: NONE

SHEET: 01/01

REV.: C