



SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			



PCB Layout

Material:

- Item ① Insulator(housing): Thermoplastic (UL94V-0)
- Item ② Spring clamp: Stainless steel
- Item ③ Terminal Body(contact pin): Brass.
- Item ④ Insulator(Cover): Thermoplastic (UL94V-0)

Electrical: cULus

- Voltage rating: 300V
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- Wire strip length: 8-9mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: 

H3 xx 1 0 x 0 xxxx G

No. OF POLES
02: 2 POLES
:
:
16: 16 POLES

COLOR —
0: BLACK
5: GREEN
6: BLUE
8: GREY

— G: Pb<40000ppm

— 0000: Standard
Any special item by
customer request.
please contact sales
department.

POLE		2	3	4	5	6	7	8
A		14.00	21.50	29.00	36.50	44.00	51.50	59.00
B		7.50	15.00	22.50	30.00	37.50	45.00	52.50
Tol.		±0.15			±0.20			
POLE	9	10	11	12	13	14	15	16
A	66.50	74.00	81.50	89.00	96.50	104.50	111.50	119.00
B	60.00	67.50	75.00	82.50	90.00	97.50	105.00	112.50
Tol.		±0.25			±0.30			

ANYTEK				CUSTOMER COPY ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD			
TITLE	H3 7.5mm Series						
PART NO.	H3xx10x0xxxxG			DWG NO.	8H30002		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Tony 2008.05.29	Tony 2008.05.29		UNIT: mm		X. ±0.50
					SCALE: NONE		X.X ±0.30
					REV.: B		X.XX ±0.10
				SHEET: 01/01			X° ±1°