




Multi-Tap Connector with Clear Insulation, Single-Sided

For Use with Aluminum or Copper Code Conductors

Type PCSB-S

- Flexible design – can be used as a tap, splice, or dead end connector
- Body made from high strength, extruded aluminum alloy to provide premium electrical and mechanical performance
- Insulated with clear PVC to eliminate the need for taping and allow for visual inspection of the complete conductor insertion
- Each port pre-filled with oxide inhibiting joint compound seals out air and moisture to deter surface oxidation
- Wide wire range-taking capability minimizes inventory requirements
- Plated steel or aluminum set screw provides high strength, durable electrical contact between conductor and connector
- UL Listed and CSA Certified for use up to 600 V and temperature rated 90°C*



Part Number	Conductor Size Range	No. of Ports	Figure Dimensions (In.)				Hex Key Size (In.)	Std. Pkg. Qty.
			L	W	H	S		
PCSB4-2S-12Y	#4 – #14 AWG STR #10 – #14 AWG SOL	2	1.23	1.25	1.25	0.53	1/8	12
PCSB4-3S-12Y		3	1.76	1.25	1.25	0.53	1/8	12
PCSB4-4S-6Y		4	2.29	1.25	1.25	0.53	1/8	6
PCSB4-5S-6Y		5	2.82	1.25	1.25	0.53	1/8	6
PCSB4-6S-6Y		6	3.35	1.25	1.25	0.53	1/8	6
PCSB4-10S-4Y		10	5.47	1.25	1.25	0.53	1/8	4
PCSB4-12S-3Y		12	6.53	1.25	1.25	0.53	1/8	3
PCSB4-14S-2Y		14	7.59	1.25	1.25	0.53	1/8	2
PCSB2/0-2S-6	2/0 – #14 AWG STR #10 – #14 AWG SOL	2	1.52	1.31	1.38	0.67	3/16	6
PCSB2/0-3S-6Y		3	2.19	1.31	1.38	0.67	3/16	6
PCSB2/0-4S-6Y		4	2.86	1.31	1.38	0.67	3/16	6
PCSB2/0-5S-4Y		5	3.53	1.31	1.38	0.67	3/16	4
PCSB2/0-6S-4Y		6	4.20	1.31	1.38	0.67	3/16	4
PCSB2/0-8S-3Y		8	5.55	1.31	1.38	0.67	3/16	3
PCSB2/0-10S-2Y		10	6.89	1.31	1.38	0.67	3/16	2
PCSB2/0-12S-1Y		12	8.24	1.31	1.38	0.67	3/16	1
PCSB2/0-14S-1Y		14	9.58	1.31	1.38	0.67	3/16	1
PCSB250-2S-6Y	250 kcmil – #10 AWG STR	2	2.03	2.00	2.13	0.94	5/16	6
PCSB250-3S-6Y		3	2.97	2.00	2.13	0.94	5/16	6
PCSB250-4S-6Y		4	3.91	2.00	2.13	0.94	5/16	6
PCSB250-5S-4Y		5	4.84	2.00	2.13	0.94	5/16	4
PCSB250-6S-4Y		6	5.78	2.00	2.13	0.94	5/16	4
PCSB250-8S-3Y		8	7.66	2.00	2.13	0.94	5/16	3
PCSB250-10S-2Y		10	9.53	2.00	2.13	0.94	5/16	2
PCSB250-12S-2Y		12	11.41	2.00	2.13	0.94	5/16	2
PCSB250-14S-1Y		14	13.29	2.00	2.13	0.94	5/16	1
PCSB350-2S-4Y	350 kcmil – #10 AWG STR	2	2.17	2.25	2.50	1.00	5/16	4
PCSB350-3S-4Y		3	3.17	2.25	2.50	1.00	5/16	4
PCSB350-4S-3Y		4	4.17	2.25	2.50	1.00	5/16	3
PCSB350-5S-3Y		5	5.17	2.25	2.50	1.00	5/16	3
PCSB350-6S-2Y		6	6.17	2.25	2.50	1.00	5/16	2
PCSB350-8S-2Y		8	8.17	2.25	2.50	1.00	5/16	2
PCSB350-10S-2Y		10	10.17	2.25	2.50	1.00	5/16	2
PCSB350-12S-1Y		12	12.17	2.25	2.50	1.00	5/16	1
PCSB350-14S-1Y		14	14.17	2.25	2.50	1.00	5/16	1
PCSB600-2S-4Y	600 kcmil – #6 AWG STR	2	2.72	2.25	2.75	1.28	3/8	4
PCSB600-3S-3Y		3	4.00	2.25	2.75	1.28	3/8	3
PCSB600-4S-2Y		4	5.28	2.25	2.75	1.28	3/8	2
PCSB600-5S-2Y		5	6.56	2.25	2.75	1.28	3/8	2
PCSB600-6S-2Y		6	7.84	2.25	2.75	1.28	3/8	2
PCSB600-8S-2Y		8	10.41	2.25	2.75	1.28	3/8	2
PCSB600-10S-1Y		10	12.97	2.25	2.75	1.28	3/8	1
PCSB600-12S-1Y		12	15.93	2.25	2.75	1.28	3/8	1
PCSB600-14S-1Y		14	18.09	2.25	2.75	1.28	3/8	1
PCSB750-2S-1	750 kcmil – #2 AWG STR	2	2.88	2.63	3.00	1.38	3/8	1

*PCSB750-2S-1 is not UL Listed or CSA Certified.