



Actuator

704.512.0



<https://eao.com/p/704.512.0>

Your product:



704.512.0
Actuator

FRONT

Front bezel material:	Plastic
Front dimension:	30 mm x 30 mm
Front bezel colour:	Grey

MOUNTING

Design:	raised
----------------	--------

OPERATING-/INDICATION PART

Lever shape:	short
Lever material:	plastic
Lever colour:	Black

ELECTRICAL CHARACTERISTICS

Standards:	The switches comply with the "Standards for low-voltage switching devices" DIN EN 60947-1
-------------------	---

MECHANICAL CHARACTERISTIC

Mechanical lifetime:	≤2.5 Mio. cycles of operation
Switching action:	Rest - Momentary
Switching positions:	2 positions
Weight:	0.034 kg
Switching angle:	42° right

AMBIENT CONDITION

IP Protection:	IP65 front side
Operating temperature:	– 40 °C ... + 55 °C
Storage temperature:	– 40 °C ... + 85 °C


OTHER

Short Description: Actuator, 30 mm x 30 mm, non illuminative, Black, short, Grey, Plastic, Rest - Momentary

max. number of switching elements: 3


Hints: Max. 3 switching elements can be clipped on

Mounting cut-outs:



A = Screw terminal
B = Push-in terminal (PIT)
C = Plug-in terminal 6.3 mm x 0.8 mm
D = Double plug-in terminal 6.3 mm x 0.8 mm


Switching positions:



Wiring diagrams:



Dimension drawings:



A = Screw terminal