





△ P.C.B. LAYOUT
Top view

N = Number of poles

Dim L = $N \times 3.81 + 2.5$

△ Dim B = $(N - 1) \times 3.81$

	Dim L	Dim B
2-5p	±0.10	±0.10
6-10p	±0.15	±0.15
11-15p	±0.20	±0.20
16-20p	±0.25	±0.25
21-24p	±0.30	±0.30

SIGN	DATE	DESCRIPTION	APPROVER
△	9/1'09	Passed Safety Approval: cULus.	Kind
△	07/23'13	change the structure///update the drawing	Da cheng
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item① Terminal body Thermoplastic (UL94V-0)
- Item② Terminal cover Thermoplastic (UL94V-0)
- △ ● Item③ Terminal lever Thermoplastic (UL94V-0)Orange(RAL2011/P)
- Item④ Solder pin Brass, Tin plated
- Item⑤ Spring clamp Stainless steel

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 6A
- Wire range:
- Solid wire(AWG): 16-26
- Stranded wire(AWG): 16-26
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- △ ● Soldering temperature: 260°C±5°C/5 Sec
- △ ● Safety Approval:
- △ ● Critical dimension:

PART NO.

HA xx 70 x 0 xxxx G			△ RoHs compliant (lead<4%) In copper Alloy
Poles	Body Color	0000 Standard @ Logo	
02 2Contacts	0 Black (RAL9005)	000A Standard ANY Logo	
03 3Contacts	2 Red (RAL3001/D)	Any special item by customer request, please contact sales department.	
	3 Orange(RAL2011/P)		
	4 Yellow(RAL1018/A)		
	5 Green(RAL6018/T)		
	6 Blue (RAL5015/A)		
	8 Grey(RAL7004/P)		
	9 White(RAL1102)		
24 24Contacts	C Multiple colors		

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	HA 3.81 Series Vertical (90D wire inlet)						
PART NO.	HAxx70x0xxxxG			DWG NO.	8HA0802		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance		
		Da cheng 2013.07.04	Da cheng 2013.07.04		UNIT: mm	X. ±0.50	
					SCALE: NONE	X.X ±0.30	
					REV.: D	X.XX ±0.10	
				SHEET: 01/01		X* ±1*	