






N=Number of contacts
Dimension A&B&C

DIM A	N×9.5+3.0
DIM B	(N-1)×9.5
DIM C	(N+2)×9.5+3.0

Poles	Tolerance
4P	±0.20
5P-10P	±0.30
11P-24P	±0.40
25P-30P	±0.60



SIGN	DATE	DESCRIPTION	APPROVER
△	04/29'11	The construction is changed here.	Tason
△	10/27'12	Change the dimensional tolerance	Jacky
△	10/27'12	Change the screw plating specification	Jacky
△	10/27'12	Add the dimensional label	Jacky
△	10/27'12	Change the electrical specification	Jacky
△	06/05'14	change the structure	Guouxu
△	06/05'14	Change the dimensional tolerance	Guouxu
△	08/26'14	The dimensional tolerance is change from 17.4±0.30 to 17.4 ^{+0.60} _{-0.30}	Airy min
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

MATERIALS ELECTRICAL
RATED VOLTAGE & CURRENT: 300 V, 20 A
WITHSTAND VOLTAGE: AC 2000 V/Min
INSULATION RESISTANCE: 1000 MΩ OR MORE AT DC 500 V
△ OPERATING TEMPERATURE RANG: -40 °C ~ +115 °C
SCREW TORQUE VALUE: 12 Lb-In.
WIRE RANGE: 22 - 12AWG
1) MOLDED PARTS: Thermoplastic, UL 94 V-0 BLACK
2) TERMINAL: BRASS, 0.8t
△ 3) TERMINAL SCREWS: STEEL, M3.5
4) COVER MATERIAL: PC

APPROVAL: us

Critical dimension: ▽

PART No.:

YK502 xx 1 x x 00G

NO. OF POLES

04: 4 POLES
04: 4 POLES
05: 5 POLES

30: 30 POLES

G:RoHS compliant(lead<4%)
in copper alloy

MARK
0: "@" MARK
1: "ANY" MARK


TERMINAL & SCREW PLATED

0: TERMINAL & SCREW: G/F
△ 1: TERMINAL: G/F, SCREW: Zinc
2: TERMINAL: Sn, SCREW: G/F
△ 3: TERMINAL: Sn, SCREW: Zinc

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		YK-502 With Flange&With Cover Series (4P-30P)			
PART NO.	YK502xx1xx00G	DWG NO.	8YK0002-502		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance
		Airy min 2014.08.26	Airy min 2014.08.26		X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°
SHEET: 01/01		UNIT: mm SCALE: NONE		REV.: F	