





SIGN	DATE	DESCRIPTION	APPROVER
	2009.1.7	APPROVAL: cULus	Kind
	11/20'12	Change the screw plating specification	Jacky
	11/20'12	Change the electrical specification	Jacky
	01/08'13	Update the drawing	Jacky
<i>THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!</i>			



SECTION:P-P



MATERIALS ELECTRICAL	
RATED VOLTAGE & CURRENT:	300 V, 15 A
WITHSTAND VOLTAGE:	AC 2000 V/Min
INSULATION RESISTANCE:	1000 MΩ OR MORE AT DC 500 V
Δ OPERATING TEMPERATURE RANGE:	-40 °C ~ +115 °C
SCREW TORQUE VALUE:	6.0Kg _f .cm
WIRE RANGE:	14 ~ 22 AWG
1) MOLDED PARTS:	THERMOPLASTIC, UL 94 V-0 BLACK
2) TERMINAL:	BRASS, 0.8t, Tin PLATED
Δ 3) TERMINAL SCREWS:	STEEL, M3

△ APPROVAL:  US

Critical dimension: ∇_C

PART No.:

YK 302xx 3 x x 00G

G RoHS compliant
(lead<4%) In copper Alloy

NO. OF POLES

02: 2 POLES
03: 3 POLES
04: 4 POLES

18: 18 POLES

— MARK

0: "@" MAK
1: "ANY" MA

— TERMINAL & SCREW PLATED

0: TERMINAL & SCREW: G/F
 ⚠ 1: TERMINAL: G/F, SCREW: Zinc
 2: TERMINAL: Sn, SCREW: G/F
 ⚠ 3: TERMINAL: Sn, SCREW: Zinc

DIM		TOL			
		2P-4P	5P-10P	11P-16P	17P-20P
Dim A	(N+2)×7.62	±0.20	±0.30	±0.40	±0.50
Dim B	(N-1)×7.62	±0.20	±0.30	±0.40	±0.50

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	YK-302 With Flange & W/o cover Series						
PART NO.	YK302xx3xx00G			DWG NO.	8YK0004-302		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Jacky 2013.01.08	Jacky 2013.01.08		UNIT: mm	X.	±0.50
					SCALE: NONE		X.X
				SHEET: 01/01	REV.: D	X.XX	±0.10
						X°	±1°