




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A1	-		A8	2825667-1 ADDED	15NOV2019	JA	PKS
			A9	ACTIVATED PART NUMBER 2825667-1	10MAR2020	PC	KR
			A10	REVISED PER ECR-20-010099	20JUL2020	BDA	KR
			A11	REVISED PER ECR-20-012333	09SEP2020	BDA	KR



- 1 SLOT ACCEPTS SINGLE OR DOUBLE COPPER MAGNET WIRE SAME DIAMETERS
NOT FOR USE WITH ALUMINUM MAGNET WIRE
- 2 IDENTIFICATION NUMBER FOR MAGNET WIRE RANGE
- 3 CONTACT CAVITY AND APPLICATION ACC. SPECIFICATION 114-94229
- 4 PCB LAYOUT, HOLES ACC. SPECIFICATION. 108-90801
- 5 CUTTING LINE: AREA WILL BE CUTTED OFF BY TERMINATION
- 6 CAVITY CENTER TO HOLE CENTER
- 7 DELIVERY STATE: STRIP ON CORRUGATED REEL WITH PAPER INTERLAYER
- 8 TO BE APPROVED, ON DEMAND BY TE ENGINEERING
- 9 MAX. 2 SPLICES PER REEL; SPLICES BE NOT BONDED TOGETHER
- 10 PRELIMINARY- NOT RELEASED FOR PRODUCTION.
- SEE TABLE



DIRECTION TOP OF REEL 1:1 	2825667-1	24	-	19,5 - 17,5; 17 	-	Ø 0.85mm to Ø 1.12mm	2120747-2
		12	-	22.5 - 20; 19,5 	-	Ø 0.63mm to Ø 0.85mm	2120746-2
	2825388-1 	10	26 - 23	26 - 22.5	Ø 0.4mm to Ø 0.56mm	Ø 0.4mm to Ø 0.63mm	2120745-2
		6	29,5 - 26,5; 26 	29,5 - 26,5; 26 	Ø 0.265mm to Ø 0.4mm	Ø 0.265mm to Ø 0.4mm	2120744-2
		4	33 - 30; 29,5 	33 - 30; 29,5 	Ø 0.18mm to Ø 0.265mm	Ø 0.18mm to Ø 0.265mm	2120743-3  2120743-2
	LOOSE PEICE PART NUMBER	IDENTI FICATION NO 	DOUBLE WIRE	SINGLE WIRE	DOUBLE WIRE	SINGLE WIRE	PART NO
		 AWG BARE WIRE RANGE		 BARE WIRE RANGE			

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±0.2
	1 PLC ±0.2
	2 PLC ±0.2
	3 PLC ±0.2
	4 PLC ±0.2
	ANGLES ±1°
MATERIAL	FINISH
CuNiSi	TINNED

DWN	H.Ballmert	28NOV2012
CHK	B.Schnaubelt	30NOV2012
APVD	T.Klenner	30NOV2012
PRODUCT SPEC		
108-94366		
APPLICATION SPEC		
-		
WEIGHT		
-		

TE Connectivity			
MAG-MATE Slim Line Contact with Multispring			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C=2120743	-
Customer Drawing		SCALE	SHEET
		5:1	1 OF 1
		REV	
		A11	