







PCB Layout

POLE		2	3	4	5	6	7	8	9	10	11	12
A		6.90	9.40	11.90	14.40	16.90	19.40	21.90	24.40	26.90	29.40	31.90
B		2.50	5.00	7.50	10.00	12.50	15.00	17.50	20.00	22.50	25.00	27.50
Tol.		±0.10					±0.15					
POLE	13	14	15	16	17	18	19	20	21	22	23	24
A	34.40	36.90	39.40	41.90	44.40	46.90	49.40	51.90	54.40	56.90	59.40	61.90
B	30.00	32.50	35.00	37.50	40.00	42.50	45.00	47.50	50.00	52.50	55.00	57.50
Tol.		±0.20					±0.30					



SIGN	DATE	DESCRIPTION	APPROVER
△	09.05.25	The voltage rating and withstanding Voltage are changed	Jacke
△	09.05.25	The Operating temperature is changed	Jacke
△	09.05.25	Add UL standard	Jacke
△	2010.03.11	Add the 2p mark	Jacke
△	2010.09.01	The design is changed	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item ③ Male contact pin: Copper Tin plated
- Item ⑥ Terminal(housing): Thermoplastic (UL94 V-0)

Electrical:	cULus
△ ● Voltage rating:	150V
● Current rating:	4A
△ ● Withstanding Voltage:	1.3KV
△ ● Operating temperature:	-40°C to +115°C
● Soldering temperature:	250°C±10°C/5 Sec
△ ● Safety Approval:	cULus

OQ xx B 1 x 1 xxxx G		G: Pb<40000ppm
No. OF POLES		
02: 2 POLES		
:		
:		
24: 24 POLES		
Color		0000: "@" Logo (Standard)
0 Black (RAL9005)		000A: "ANYTEK" Mark
2 Red (RAL3001/D)		Any special item by
3 Orange(RAL2011/P)		customer request.
4 Yellow(RAL1018/A)		please contact sales
5 Green(RAL6018/T)		department.
6 Blue (RAL5015/A)		
8 Grey(RAL7035/D)		

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		OQ 2.5mm 90° Series											
PART NO.		OQxxB1x1xxxxG					DWG NO.		80Q0901				
APPROVED		CHECKED	DESIGNED	DRAWN		CUST NO.		Tolerance					
			Jacke 2010.09.01	Jacke 2009.05.25				UNIT: mm		X. ±0.50			
								SCALE: NONE		X.X ±0.30			
						SHEET: 01/01		REV.: E		X.XX ±0.10			
										X° ±1°			