

SUMMARY

Wires

Low	4
High	0
Coax	0
Triax	0
Quad	0
Fiber	0
Fluidic	0
Material	Brass



Series	
Termination type	Male crimp
IP rating	50
Cable Ø (mm)	5.30 - 5.60
Wire size / AWG	26.00 - 22.00

TECHNICAL DETAILS

Mechanics

Shell Style/Model	FG*: Straight plug, cable collet and nut for fitting a bend relief
Keying	2 keys (alpha=90, plug: male contacts, receptacle: female contacts)
Housing Material	Brass (chrome plated) shell and collet nut, nickel plated brass latch sleeve and mid pieces
Cable Fixing	: 5.3 - 5.6 mm
Variant	Z : Nut for fitting a bend relief

Performance

Configuration	0B.304 : 4 Low Voltage
Insulator	Y: PEEK for crimp contacts
Rated Current	7

Specifications

Contact Type:	Crimp
Max. Matings:	5000
Contact Retention:	22 N
Contact Dia.:	0.7 mm (0.028in)
Bucket Dia.:	0.8 mm (0.031in)
Min. Conductor:	0.14 mm ² (AWG 26)
Max. Conductor:	0.34 mm ² (AWG 22)
R (max):	6.1 mOhm
Vtest (contact-contact):	1350 V (AC), 1910 V (DC)
Vtest (contact-shell):	700 V (AC), 990 V (DC)


Others

Humidity (max):	<=95% [at 60 deg C / 140 F]
Vibration:	15 g [10 Hz - 2000 Hz]

Shock Resistance: 100 g [6 ms]
Salt Spray Corrosion: >144 hr
Climatical Category: 50/175/21
Shielding (min): 75 dB (10 MHz)
Shielding (min): 40 dB (1 GHz)
IP Rating: 50

DRAWINGS

Draws



Dimensions

	A	L	M	S1	S2
mm.	9.5	35	25	8	7
in.	0.37	1.38	0.98	0.31	0.28

RECOMMENDED BY LEMO

Tools

Crimp Tool: DPC.91.701.V
Positionner: DCE.91.070.BVC
Extractor: DCF.91.070.2LT
Spanner: DCP.91.001.TN

Cables

004 220	PVC	Black	
BELDEN 9804	PVC	Grey	
CMU.04.075.054NB	PVC	Black	

