


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:


1. ANTI-OXIDANT JOINT COMPOUND RECOMMENDED FOR ALL ALUMINUM CONNECTORS
2. SPLICER REDUCER AND SCREWS ARE TIN PLATED ALUMINUM
3. MADE IN U.S.A.
4. LISTED PER UL486B
5. CSA CERTIFIED
(NOTE: DOES NOT APPLY TO SR-4/0-XY)
6. THIS PART IS RoHS COMPLIANT

PANDUIT PART NUMBER	FIGURE	WIRE RANGE CU AND AL	INSTALLATION TOOL	WIRE STRIP LENGTH	DIMENSIONS - IN		
					A	B	C
SR-2-XY	1	2 - 14 AWG STRANDED 10 - 14 AWG SOLID	SINGLE BLADE SCREWDRIVER	0.63	0.50	1.38	0.56
SR-0-XY		1/0 - 14 AWG STRANDED 10 - 14 AWG SOLID		0.88	0.75	1.91	0.75
*SR-4/0-XY		2	4/0 - 6 AWG STRANDED	5/16" HEX ALLEN WRENCH	1.08	1.00	2.31
SR-250-XY	250 kcmil - 6 AWG STRANDED		1.90		1.00	3.94	1.13
SR-350-XY	350 kcmil - 6 AWG STRANDED		2.00		1.13	4.19	1.19
SR-500-3Y	500 kcmil - 3/0 AWG STRANDED		3/8" HEX ALLEN WRENCH	2.44	1.37	5.00	1.40
SR-750-1Y	750 kcmil - 250 kcmil STRANDED		1/2" HEX ALLEN WRENCH	3.06	1.63	6.25	1.75
SR-1000-1Y	3		1000 kcmil - 500 kcmil STRANDED	9/16" HEX ALLEN WRENCH	4.38	1.72	8.69



CERTIFIED

(*DOES NOT APPLY TO SR-4/0-XY)

							TITLE ALUMINUM SPLICER REDUCER SR SERIES CUSTOMER DRAWING								
							ITEM REVISION NAME N41540BA/03			<div>PANDUIT</div>					
							DATASET FILE NAME C41540/03.SLDDRW								
03	7/15	JHNU	JHNU	RGB	REVISED PART NUMBER: SR-0-XY WAS SR-0-SY	N41540BA-C41540	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .XX ± .02 ANGLES ±  THIRD ANGLE PROJECTION							MATERIAL SEE NOTES	
02	9/14	JHNU	JHNU	RGB	ADDED NOTE TO SPECIFY SR-4/0-XY IS NOT CSA CERTIFIED CONVERTED TO SOLIDWORKS REVISED DWG SIZE: WAS A SIZE	N41540BA-C41540								DRAWING NUMBER C41540	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY JHNU		DATE 10/05	CHK LEM	SCALE N/A	SHEET 1 OF 1		SIZE B	