

N = Number of poles



Poles	Tolerance
2p-4p	± 0.15
5p-8p	± 0.20
9p-12p	± 0.30
13p-16p	± 0.40

SIGN	DATE	DESCRIPTION	APPROVER
△	1/26'07	Dimension changed from 4.0 to 3.5	Tony
△	1/26'07	Soldering temperature changed from 245° to 250°	Tony
△	6/30'08	Operating temperature is changed	Marvin
△	6/30'08	With flange body is changed	Marvin
△	4/06'09	Added TUV standard	Jacke
△	2009.08.28	The design is changed from the round hole to hexagonal hole	Jacke
△	2009.10.21	The material is changed from Brass to Copper	Jacke
△	2010.12.08	The design is changed	Chen Bo
△	2010.12.08	The design is changed	Chen Bo
△	12/05'11	The Dim C & D & dimension 7.62 are added	ChenMing
△	12/05'11	Flange nut is changed	ChenMing

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- ⚠ ● Item Ⓐ Male contact pin: Copper Tin plated
- Item Ⓑ Terminal(housing): Thermoplastic (UL94V-0)
- Item Ⓒ With flange nut: Brass ,M2.5

- | | | | |
|---|--------------------------|---|---|
| ⚠ | Electrical: | cULus | TUV |
| ● | Voltage rating: | 300V | 750V |
| ● | Current rating: | 20A | 15A |
| ● | Withstanding Voltage: | 1.6 KV | 6KV |
| ⚠ | ● Operating temperature: | -40°C to +115°C | |
| ⚠ | ● Soldering temperature: | 250°C±10°C/5 Sec | |
| ● | Safety Approval: |  |  |
| ● | Critical dimension: | ▽ | |

OQ xx 0 5 x 1 xxxx G

No. OF POLES
02: 2 POLES
:
:
16: 16 POLES

COLOR

- 0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)
C Green(RAL6018/U)


— G: Pb<40000ppm

0000: "@ " Logo (Standard)
000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		OQ 7.62mm 90° /with flange Series 2p~16p					
PART NO.		OQxx05x1xxxxG		DWG NO.		80Q0305	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance		
			ChenMing 2011.12.05		UNIT: mm	X.	±0.50
					SCALE: NONE	X.X	±0.30
					REV: J	X.XX	±0.10
			SHEET: 01/01			X°	±1°