




SIGN	DATE	DESCRIPTION	APPROVER
△	6/30'09	Withstanding Voltage changed from 1.6KV to 1.32KV.	Kind
△	9/26'09	The spring clamp changed.	Kind
△	11/25'09	The Grey code changed from RAL7004/P to RAL 7035/D.	Kind
△	07/30'10	2P~6P add rid	Runner
△	8/05'13	update the drawing	Da cheng

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item △ Terminal lever: Thermoplastic (UL94V-0) Orange(RAL 2011/P)
 - Item ② Terminal top housing: Thermoplastic (UL94V-0)
 - Item ③ Female contact : PhBz Tin Plated.
 - Item ④ Spring clamp : Stainless steel
 - Item ⑤ Terminal down housing: Thermoplastic (UL94V-0)
- Electrical: cULus

- Voltage rating: 160 V
- Current rating: 5.5 A
- Wire range:
- Solid wire(AWG): 16-24
- Stranded wire(AWG): 16-24
- Wire strip length: 9-10 mm

- △ Withstanding Voltage: 1.32 KV
- Operating temperature: -40°C to +115°C
- APPROVAL:

- △ Critical dimension:

KD xx 1 0 x 0 xxxx G

No. OF POLES
02: 2 POLES
:
24: 24 POLES

COLOR
0: BLACK
5: GREEN (RAL 6018/T)
6: BLUE
△ 8: GREY (RAL 7035/D)

RoHS compliant
(lead<4%)
In copper Alloy

0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

△	DimL=(N-1)×3.5+4.2
	DimP=(N-1)×3.5

N=Number of poles

POLES	Dim. Tol	Dim.L/P
2p-6p		±0.15
7p-12p		±0.25
13p-18p		±0.30
19p-24p		±0.40

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	KD 3.5mm W/O Flange Series						
PART NO.	KDxx10x0xxxxG			DWG NO.	8KD0001		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		Da cheng 2013.08.05	Da cheng 2013.08.05		UNIT: mm SCALE: NONE	Tolerance	
						X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°	
				SHEET: 01/01	REV.: G		