

Specification for Approval

Customer:	
Customer P/N:	
EEC P/N:	SQ24701N0
Spec No.:	
Version No.:	V0.1
Description:	2.5/5G BASE-T
	Laser Marking

Customer Approval		EEC Approval	
Inspected By:		Issued By:	Xingyu,He
Checked By:		Checked By:	Duffy
Approved By:		Approved By:	Jerry
Approved Date:		Issued Date:	2024/7/15

Please Return One Copy to Us After Approved,TKS! (承认后请回寄一份,谢谢)

- Remark:
- 1. Before use, please confirm whether this product is suitable for your design, Scientic only ensure products meet this specification.
 - 2. This specification data change must be confirmed by both parties,any individual modification is invalid.
 - 3. If customer placed orders without signing back this specification, it is regarded as recognition.





绵阳敦源电子科技有限公司
Mianyang Dunyuan Electronics Technology Co.,Ltd
地址：四川省绵阳市高新区综合保税区
ADD: Comprehensive Bonded Zone, High-Tech Industrial Development Zone Mianyang, SiChuan


[illegible]

DESCRIPTION	EEC P/N:	SPEC NO	Version No.: V0.1
2.5/5G BASE-T	SQ24701N0		PAGE: 1/4

A. MECHANICAL(unit:mm)



B. SCHEMATICS




DESCRIPTION	EEC P/N:	SPEC NO	Version No.: V0.1
2.5/5G BASE-T	SQ24701N0		PAGE: 2/4

C. ELECTRICAL SPECIFICATIONS @25°C

Unless Otherwise Specified, Testing is Performed at 25°C ± 5°C

1. OCL: 200uH Min @ 100KHz, 0.1V
2. Leakage Inductance: 0.5uH Max @ 100KHz, 0.1V
3. DCR: 1000mΩ Max
4. Turns Ratio: 1CT:1CT±5%
5. Insertion Loss: -1.0 dB Max @ 1-100 MHz
-2.0 dB Max @ 100-250 MHz
6. Return Loss: -16 dB Min @ $1 \leq f \leq 40$ MHz
-16+10log(f/40) dB Min @ $40 < f \leq 250$ MHz, where f is in MHz
7. Cross Talk: -30 dB Typ @ 1-250 MHz
8. Common Mode Rejection Ratio: -30 dB Typ @ 1-250 MHz
9. Isolation Hipot: 1500VAC 1mA 60S
10. Operating temperature 0°C to +70°C
11. Storage temperature -40°C to +85°C

D. RECOMMEND REFLOW SOLDERING CURVE

MSL:

Grade: 1 level. Floor life: 0.5 year Condition: ≤30°C/60%RH.


Ramp up rate=3°C/s max Ramp down rate=6°C/s max

TL=217°C tL=60s-150s Tp=250+/-3°C Time within 5°C of actual Peak Temperature (tp): 20~40s

Ts min=150°C Ts max=200°C Ts min to Ts max: 60s-180s, 25°C to peak Temperature: 8minutes max

DESCRIPTION	EEC P/N:	SPEC NO	Version No.: V0.1
2.5/5G BASE-T	SQ24701N0		PAGE: 3/4

E. PACKAGE INFORMATION



Package Quantity:

One Reel=350Pcs

One Inner Carton=350*2=700Pcs

One Export Carton=700*5=3500Pcs

DESCRIPTION	EEC P/N:	SPEC NO	Version No.: V0.1
2.5/5G BASE-T	SQ24701N0		PAGE: 4/4