

PACT MCR-V2-5012- 85- 200-5A-1 - Current transformer



2276120

<https://www.phoenixcontact.com/us/products/2276120>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Window-type current transformer, 200 A AC primary current; 5 A AC secondary current; accuracy class 1; 5 VA rated power

Commercial data

Item number	2276120
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C444
Product key	CK4A11
Catalog page	Page 214 (C-5-2019)
GTIN	4046356502757
Weight per piece (including packing)	520.4 g
Weight per piece (excluding packing)	445.3 g
Customs tariff number	85043129
Country of origin	DE

PACT MCR-V2-5012- 85- 200-5A-1 - Current transformer



2276120

<https://www.phoenixcontact.com/us/products/2276120>

Technical data

Product properties

Product type	Current transformer
Data management status	
Article revision	04

Electrical properties

Rated insulation voltage	1 kV (Phase/neutral conductor)
General	
Can be calibrated	no
Converter type	Window-type current transformer

Input data

Current transformer	
Rated power	5 VA
Thermal rated short-time current	$I_{th} = 60 * I_n$
Thermal rated continuous current	$I_d = 1.2 * I_n$
Rated surge current	$I_{dyn} = 2.5 * I_{th}$
Rated frequency f_n	50 Hz 60 Hz
Primary rated current I_{pn}	0 A AC ... 200 A AC
Can be calibrated	no
Converter type	Window-type current transformer

Output data

Signal	
Designation	Current output
Secondary rated current I_{sn}	5 A AC
Surge current limitation factor	FS 5
Accuracy class	1

Connection data

Connection method	Screw connection
Conductor cross section flexible	2x 2.5 mm ² ... 4 mm ² (Secondary terminals with screw connection)

Dimensions

Item dimensions	
Width	30 mm
Height	108 mm
Depth	85 mm

PACT MCR-V2-5012- 85- 200-5A-1 - Current transformer



2276120

<https://www.phoenixcontact.com/us/products/2276120>

Item dimensions with alternative mounting

Width	85 mm
Height	108 mm
Depth	30 mm

Copper rail

Width	50 mm
Height	12 mm

Copper rail 2

Width	40 mm
Height	10 mm

Circular conductor

Diameter	42 mm
----------	-------

Material specifications

Color	black (RAL 9005)
Housing material	PA 6.6

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 40 °C
Ambient temperature (storage/transport)	-25 °C ... 40 °C
Altitude	≤ 1000 m
Permissible humidity (operation)	Use only indoors, non-condensing
Insulating material class	E

Approvals

UL, USA/Canada

Identification	XODW8.E323953
----------------	---------------

Standards and regulations

Standards/regulations	EN 61869
-----------------------	----------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

PACT MCR-V2-5012- 85- 200-5A-1 - Current transformer




2276120

<https://www.phoenixcontact.com/us/products/2276120>

Drawings

Dimensional drawing



PACT MCR-V2-5012- 85- 200-5A-1 - Current transformer



2276120

<https://www.phoenixcontact.com/us/products/2276120>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2276120>



EAC

Approval ID: RU*DE*08.B.01187/19

PACT MCR-V2-5012- 85- 200-5A-1 - Current transformer



2276120

<https://www.phoenixcontact.com/us/products/2276120>

Classifications

ECLASS

ECLASS-11.0	27210902
ECLASS-13.0	27210902
ECLASS-12.0	27210902

ETIM

ETIM 9.0	EC002048
----------	----------

UNSPSC

UNSPSC 21.0	39121000
-------------	----------

PACT MCR-V2-5012- 85- 200-5A-1 - Current transformer



2276120

<https://www.phoenixcontact.com/us/products/2276120>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com