






LOC	DIST	REVISIONS						
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD	
			A1	REVISED PER ECO-09-025699	11-DEC-2009	KK	AEG	
			A2	REVISED PER ECO-12-010437	28SEP2012	CJV	DLG	

- 1 MATERIAL: LCP, BLACK.
- 2 MATERIAL: PHOSPHOR BRONZE PER ASTM B 103.
- 3 FINISH: 0.76µm MIN GOLD PLATE PER ASTM B 488, APPLIES TO INTERFACE AREA AND 2.03µm MIN TIN PLATE SOLDER TAILS, ALL OVER 3.81µm MIN NICKEL PLATE PER QQ-N-290.
- 4 DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER.
- 5 WITH KAPTON PLACEMENT DOT INSTALLED.
- 6 PACKAGED IN TUBES.
- 7 PACKAGED IN TAPE AND REEL.
- 8 CONNECTOR PIN IDENTIFIERS: SYMETRICAL VERTICAL CONNECTORS CAN BE APPLIED TO BOARD IN EITHER ORIENTATION.
- 9 FINISH: 0.38µm MIN GOLD PLATE PER ASTM B 488, APPLIES TO INTERFACE AREA AND 2.03µm MIN TIN PLATE SOLDER TAILS, ALL OVER 3.81µm MIN NICKEL PLATE PER QQ-N-290.
- 10 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



		7	-	-	-	-	-	-	-	1888020-6	5	1888020-8
OBSOLETE	9	7	-	-	-	-	-	-	-	1888020-5	5	1888020-7
		6	36	16	17.4	8	36	15.8	36	-		1888020-6
OBSOLETE		6	26	12	13.4	6	26	11.8	26	-		1888020-5
	3	7	-	-	-	-	-	-	-	1888020-2	5	1888020-4
OBSOLETE		7	-	-	-	-	-	-	-	1888020-1	5	1888020-3
		6	36	16	17.4	8	36	15.8	36	-		1888020-2
10 OBSOLETE		6	26	12	13.4	6	26	11.8	26	-		1888020-1
	FINISH	PACKAGING	N	E	D	C	B	A	POSN	MADE FROM		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009.				DWN M.E. CONNER 01JUL05		CHK R.R. HENRY 01JUL05		TE Connectivity			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R.R. HENRY 01JUL05		NAME		EVERCLEAR Mini-SAS VERTICAL RECEPTACLE CONNECTOR ASSEMBLY, SURFACE MOUNT			
mm		0 PLC ±		PRODUCT SPEC		SIZE		CAGE CODE DRAWING NO			
mm		1 PLC ±		APPLICATION SPEC		RESTRICTED TO		A100779C=1888020			
mm		2 PLC ±		WEIGHT		SCALE		10:1			
mm		3 PLC ±		CUSTOMER DRAWING		SHEET		1 OF 2			
mm		4 PLC ±				REV		A2			
mm		ANGLES									
MATERIAL		FINISH									
SEE NOTES		SEE TABLE									

