

Printed-circuit board connector - MVSTBR 2,5/ 4-ST-5,08 BD2: +STC - 1706689

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



PCB connector, nominal current: 12 A, rated voltage (III/2): 320 V, number of positions: 4, pitch: 5.08 mm, connection method: Screw connection with tension sleeve, color: green, contact surface: Tin


The figure shows a 10-position version of the product

Your advantages

- ✓ Well-known connection principle allows worldwide use
- ✓ Low temperature rise, thanks to maximum contact force
- ✓ Allows connection of two conductors



Key Commercial Data

| | |
|----------------------|---|
| Packing unit | 1 |
| GTIN |  4 055626 170909 |
| GTIN | 4055626170909 |
| Custom tariff number | 85366990 |

Technical data

Dimensions

| | |
|--------------|----------|
| Length [l] | 12.5 mm |
| Width [w] | 20.32 mm |
| Height [h] | 26 mm |
| Pitch | 5.08 mm |
| Dimension a | 15.24 mm |

General

| | |
|---------------------|--------------------------------------|
| Range of articles | MVSTBR 2,5/...-ST |
| Number of positions | 4 |
| Connection method | Screw connection with tension sleeve |

Printed-circuit board connector - MVSTBR 2,5/ 4-ST-5,08 BD2: +STC - 1706689

Technical data

General

| | |
|--|---------------------|
| Insulating material group | I |
| Rated voltage (III/2) | 320 V |
| Nominal current I _N | 12 A |
| Nominal cross section | 2.5 mm ² |
| Flammability rating according to UL 94 | V0 |

Standards and Regulations

| | |
|--|----|
| Flammability rating according to UL 94 | V0 |
|--|----|

Environmental Product Compliance

| | |
|------------|---|
| REACH SVHC | Lead 7439-92-1 |
| China RoHS | Environmentally Friendly Use Period = 50 |
| | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 5.1 | 27260700 |
| eCl@ss 6.0 | 27260700 |
| eCl@ss 7.0 | 27440309 |
| eCl@ss 8.0 | 27440309 |
| eCl@ss 9.0 | 27440309 |

ETIM

| | |
|----------|----------|
| ETIM 5.0 | EC002638 |
| ETIM 6.0 | EC002638 |

UNSPSC

| | |
|-------------|----------|
| UNSPSC 13.2 | 39121409 |
|-------------|----------|

Approvals

Approvals

Approvals


EAC

Ex Approvals

Printed-circuit board connector - MVSTBR 2,5/ 4-ST-5,08 BD2: +STC - 1706689

Approvals

Approval details

| | | |
|-----|---|---------|
| EAC |  | B.01742 |
|-----|---|---------|