




SIGN	DATE	DESCRIPTION	APPROVER
△	2009.09.07	The design is changed	Jacke
△	2009.09.07	The electrical is changed	Jacke
△	2010.03.31	Add the 2p mark	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Materials

- Item a Terminal body:Thermoplastic (UL94V-0)
Item b Terminal Cover:Thermoplastic (UL94V-0)
Item c Female contact:PhBz(CuSn), Tin plated

Electrical

- Voltage rating: 300VAC
- Current rating: 20A
- Withstanding Voltage: 1.6kv
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: 

V7 xx 0 1 x 0 xxxx G

No. OF POLES
02 2 CONTACTS
03 3 CONTACTS
...
16 16 CONTACTS

Color

- 0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)


G: Pb<40000ppm

0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

ANYTEK

INSPECTION COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		V7 7.62 W/O flange Series Vertical (2P~16P)							
PART NO.		V7xx01x0xxxxG			DWG NO.		8V70501		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.				Tolerance	
		Jacke 2010.03.31	Jacke 2009.09.07		UNIT: mm		X. ±0.5		
					SCALE: None		X.X ±0.3		
				SHEET: 01/01	REV.: D		X.XX ±0.1		
							X° ±1°		

POLE	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16
B	7.62	15.24	22.86	30.48	38.1	45.72	53.34	60.96	68.58	76.2	83.82	91.44	99.06	106.68	114.3
A	13.34	20.96	28.58	36.2	43.82	51.44	59.06	66.68	74.3	81.92	89.54	97.16	104.78	112.4	120.02
Tol.	±0.15					±0.20					±0.30				