

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSFERRED TO
OTHER DOCUMENTS OR DISCLOSED TO
OTHERS OR USED FOR ANY PURPOSE
OTHER THAN THAT FOR WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED
WRITTEN CONSENT OF SAMTEC INC.






FIG. 1
(THROUGH HOLE)

- 1.) MAX ALLOWABLE BOW AFTER ASSEMBLY: .005 IN/IN.
- 2.) TERMINAL PUSHOUT FORCE: 2 lbs. MIN.
- 3.) MAX PIN ROTATION IN BODY: 2°.
- 4.)  REPRESENTS A CRITICAL DIMENSION.
- 5.) MAX CUT FLASH: .010.
- 6.) GOLD CONTACT AREA LOCATION FOR G, H, S, L, F, SM, LM, FM, & STL PLATINGS.
- 7.) ORIENTATE PINS TO PREVENT BANDOLIER MARKS FROM SHOWING IN THE POST AREA.
(SEE TABLE 2)

LEAD	TERMINAL 1	TERMINAL 2	"L"	"A"	"B"	"C"
-05	T-1S6-21-XXX-2	N/A	.335	.105	.170	.050
-06	T-1S6-18-XXX-2	N/A	.300	.105	.135	.050
-01-S	T-1S6-22-XXX-2	N/A	.495	.230	N/A	.165
-01-D	T-1S6-22-XXX-2	-----	.495	.230	N/A	.165
-01-D	-----	T-1S6-23-XXX-2	.695	.230	N/A	.165



—S: SINGLE



-D: DOUBLE

MATERIAL:
INSULATOR:
LIQUID CRYSTAL POLYMER
COLOR: BLACK

TERMINALS:
PHOSPHOR BRONZE

EXIST

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

SHEET 1 OF 3