

INTERCONNECTS

SERIES 316 • .100" GRID ELEVATED • SINGLE ROW STRIPS




FIG. 1




FIG. 2




FIG. 3




FIG. 4





FIG. 5

- Elevated socket strips are available in 5 different heights:

316...006 uses pin # 0153-1
 316...003 uses pin # 0153-2
 316...007 uses pin # 0153-3
 316...008 uses pin # 0153-4
 316...001 uses pin # 0153-5
 See page 167 for details

- Hi-Rel, 4-finger BeCu #30 contact is rated at 3 amps. See page 253 for details

- Insulators are high temperature thermoplastic, suitable for all soldering operations



ORDERING INFORMATION

FIG. 1	Series 316...006	Standoff Height = .236
	316-XX-1	-41-006000 Specify number of pins 01-64
FIG. 2	Series 316...003	Standoff Height = .315
	316-XX-1	-41-003000 Specify number of pins 01-64
FIG. 3	Series 316...007	Standoff Height = .402
	316-XX-1	-41-007000 Specify number of pins 01-64
FIG. 4	Series 316...008	Standoff Height = .472
	316-XX-1	-41-008000 Specify number of pins 01-64
FIG. 5	Series 316...001	Standoff Height = .594
	316-XX-1	-41-001000 Specify number of pins 01-64
RoHS-2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Environmental Data, See page 264		
SPECIFY PLATING CODE XX=		
Sleeve (Pin)	91	93
Contact (Clip)	41	43
	47	
	200 μ"Sn/Pb	200 μ"Sn/Pb
	200 μ"Sn	200 μ"Sn
	10 μ" Au	30 μ" Au
	30 μ" Au	Au Flash