

Han 3EMC-PFT-SL-M20 (M4)



Image is for illustration purposes only. Please refer to product description.

Identification

Category	Hoods / Housings
Series of hoods/housings	Han® EMC
Type of hood/housing	Panel feed through housing
Description of hood/housing	Fixing hole for M4 screw

Version

Size	3 A
Version	Top entry
Number of cable entries	1
Cable entry	1x M20
Locking type	Single locking lever
Field of application	Hoods/Housings for higher EMC requirements
Pack contents	Please order seal screw separately.

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP44 IP65 With seal screw IP67 With seal screw
Type rating acc. to UL 50 / UL 50E	12

Material properties

Material (hood/housing)	Zinc die-cast
-------------------------	---------------

Material properties

Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
Material (seal)	NBR
Material (locking)	Steel
Surface (locking)	Zinc plated
RoHS	compliant with exemption
RoHS exemptions	6(a) / 6(a)-I: Lead as an alloying element in steel for machining purposes and in galvanised steel containing up to 0,35 % lead by weight / Lead as an alloying element in steel for machining purposes containing up to 0,35 % lead by weight and in batch hot dip galvanised steel components containing up to 0,2 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel Naphthalene

Specifications and approvals

Approvals	CE DNV GL
-----------	--------------

Commercial data

Packaging size	10
Net weight	90 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140132283
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors