






TW-TH Series - 2,00 mm Flex Stack, Flexible Board
Stacker, Through-hole
TW-TH Series

PDF DATASHEET

© 1992-2015 CADENAS GmbH
Last Modification (geometry): 17/09/2014 10:35
Datasheet creation date: 29/10/2015 06:00






LEAD STYLE	OAL
-01	(8,20) .323
-02	(9,60) .377
-03	(13,60) .535
-04	(14,10) .555
-05	(15,10) .594
-06	(17,10) .673
-07	(19,10) .751
-08	(21,10) .830
-09	(11,60) .456
-10	(15,60) .614
-11	(10,08) .397
-12	(28,19) 1.110

x Style -08 & -12 = S & D only

ROW OPTION	STACKER HEIGHT
-S, -Dx, & -Q	(3,05) .120 MIN
-T, -5, -6	(4,06) .160 MIN

x -D with stacker height greater than (4,06mm) .160" will not have standoffs.





**TW-TH Series - 2,00 mm Flex Stack, Flexible Board
Stacker, Through-hole**
TW-TH Series

PDF DATASHEET

© 1992-2015 CADENAS GmbH

Last Modification (geometry): 17/09/2014 10:35

Datasheet creation date: 29/10/2015 06:00

PN (Part Number)	TW-05-03-G-D-240-090
SERIES (Series)	TW-TH
POS (No. Pins per Row)	05
LS (Lead Style)	03
PLOPT (Plating Option)	-G: 20u" Gold in Contact Area, 3u Gold on Tail (Non-standard option - Please contact SAMTEC)
ROW (Row Option)	D:Double Row
SH (Stacker Height)	240
TL (Tail Length)	090
POLOPT (Polarized Position)	Not Selected



Bill of material

N°	Description	Amount
1	TW-05-03-G-D-240-090	1