




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	REV PER ECO 13-001557	2-12-13	CT	DM
			C	REVISED PER ECO-15-013009	03DEC15	RS	CT




—RED FULL MATE INDICATOR



-SEE DETAIL A




DETAIL A
SCALE 6:1





—PIN CONTACTS
(2102349-3)

KEY OPTION	KEY ROTATION	
	"R"	"S"
NORMAL	150°	210°
A	140°	215°
B	132°	248°



JAM NUT-
SEE TABLE
FOR FINISH




—RECEPTACLE ASSEMBLY
ALUMINUM SHELL
SEE TABLE FOR FINISH

—1 1/16" - 24 THREADS

[illegible]

1. -1, -3 AND -5 ARE ELECTROLESS NICKEL PLATE PER MIL-C-26074.
2. -2, -4 AND -6 ARE BLACK ZINC NICKEL PER AMS-2417.
3. O-RING AND NUT ARE ASSEMBLED TO SHELL. CONTACTS SHALL BE PACKAGED SEPARATELY IN KIT.



1 / 8" MAX PANEL THICKNESS

1	-	1	10	B	BLACK ZINC NICKEL PLATE	2102352-6
-	1	1	10	B	NICKEL PLATE	2102352-5
1	-	1	10	A	BLACK ZINC NICKEL PLATE	2102352-4
-	1	1	10	A	NICKEL PLATE	2102352-3
1	-	1	10	NORMAL	BLACK ZINC NICKEL PLATE	2102352-2
-	1	1	10	NORMAL	NICKEL PLATE	2102352-1
JAM NUT BLACK ZINC NICKEL PLATE	JAM NUT NICKEL PLATE	O-RING FLUROSILICONE	PIN CONTACT 50 μ GOLD PLATE	KEYING OPTION	FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M (ISO STANDARDS)			DWN MCKIBBEN, JOHN 09 JUN 2011		 TE Connectivity							
DIMENSIONS: INCHES [mm]			CHK DOWHOWER, KENNETH 09 JUN 2011									
			TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD DOWHOWER, KENNETH 09 JUN 2011		NAME RECEPTACLE ASSEMBLY KIT					
			PRODUCT SPEC		SIZE							
			108-2482		CAGE CODE							
MATERIAL			APPLICATION SPEC		DRAWING NO		RESTRICTED TO					
			114-32025		A200779							
			WEIGHT		C-2102352							
FINISH			CUSTOMER DRAWING		SCALE		SHEET		OF		REV	
-			-		2:1		1		1		C	