

4

3

2

1


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
IS	-		-	SEE SHEET 1	-	-

V23614-B109-P25 	9-1393670-0	ST214	3.8	7.93	114-71012	Dielectric	PTFE	-
						Outer Con.	CuBe/ Bronze	min. 0.2 μm Au over PdNi in contact area
						Center Con.	Cu Be Brass	min. 0.1 μm Au over min. 2 μm NiP
V23614-B109-P23 	8-1393670-9	ST212	2.15	4.45	114-71012	Dielectric	PTFE	-
						Outer Con.	CuBe/ Bronze	min. 0.2 μm Au over PdNi in contact area
						Center Con.	Cu Be Brass	min. 0.1 μm Au over min. 2 μm NiP
V23614-B102-P76 	8-1393670-8	02Y(ST)CY 0.45/2.0	2.15	5.2	114-71009	Dielectric	PTFE	-
						Outer Con.	CuBe/ Bronze	min. 0.2 μm Au over PdNi in contact area
						Center Con.	Cu Be Brass	min. 0.1 μm Au over min. 2 μm NiP
V23614-A109-P25 	6-1393670-7	ST214	3.8	7.93	114-71012	Dielectric	PTFE	-
						Outer Con.	CuBe/ Bronze	min. 0.2 μm Au over PdNi in contact area
						Center Con.	Cu Be Brass	min. 0.1 μm Au over min. 2 μm NiP
V23614-A109-P23A 	6-1393670-6	ST212	2.15	4.45	114-71012	Dielectric	PTFE	-
						Outer Con.	CuBe/ Bronze	min. 0.2 μm Au over PdNi in contact area
						Center Con.	Cu Be Brass	min. 0.1 μm Au over min. 2 μm NiP
V23614-A109-P23 	6-1393670-5	ST212	2.15	4.45	114-71012	Dielectric	PTFE	-
						Outer Con.	CuBe/ Bronze	min. 0.2 μm Au over PdNi in contact area
						Center Con.	Cu Be Brass	min. 0.1 μm Au over min. 2 μm NiP
Old Nr	TE Nr	Cable Type	Dim a	Dim b	Appl. Spec.	Description	Material	Plating

OBSOLETE

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm



MATERIAL
-

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±0.5
2 PLC ±0.13
3 PLC ±0.013
4 PLC ±0.0001
ANGLES ±-
FINISH
-

DWN MOROBE 2APR2001
CHK MATTHEEWS 5APR2001
APVD BOZZER 5APR2001
PRODUCT SPEC 108-71032
APPLICATION SPEC SEE TABLE
WEIGHT -

 Tyco Electronics
CH - Switzerland - Lugano

NAME
CABLE PLUG
SNAP-ON COUPLING
1.0/2.3 75 Ohm

SIZE A3
CAGE CODE 00779
DRAWING NO C-5-1393670-7
RESTRICTED TO -

SCALE 5:1
SHEET 2 OF 3
REV B6

AMP 1470-19 REV 31MAR2000

4

3

2


1

LOC IS	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—

5	619353-1	RG179D	1.7	4.45	114-71009	Dielectric	PTFE	-
						Outer Con.	CuBe/ Bronze	min. 0.2µm Au over PdNi in contact area
						Center Con.	Cu Be Brass	min. 0.1µm Au over min. 2µm NiP
5	619086-1	7 02Y12YC(mS) C6Y 0.45/2.0 BT 3002 TZC 750 24	2.1	5.2	114-71009	Dielectric	PTFE	-
						Outer Con.	CuBe/ Bronze	min. 0.2µm Au over PdNi in contact area
						Center Con.	Cu Be Brass	min. 0.1µm Au over min. 2µm NiP
5	V23614-C 109-P23	9-1393670-5	2.15	4.45	114-71012	Dielectric	PTFE	-
						Outer Con.	CuBe/ Bronze	min. 0.2µm Au over PdNi in contact area
						Center Con.	Cu Be Brass	min. 0.1µm Au over min. 2µm NiP
5	V23614-C 102-P76	9-1393670-4	2.15	5.2	114-71009	Dielectric	PTFE	-
						Outer Con.	CuBe/ Bronze	min. 0.2µm Au over PdNi in contact area
						Center Con.	Cu Be Brass	min. 0.1µm Au over min. 2µm NiP
Old Nr	TE Nr	Cable Type	Dim a	Dim b	Appl. Spec.	Description	Material	Plating

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±0.5

2 PLC ±0.13

3 PLC ±0.013

4 PLC ±0.0001

ANGLES ±

MATERIAL -

FINISH -

DWN MOROBE 2APR2001

CHK MATTHEEUWS 5APR2001

APVD BOZZER 5APR2001

PRODUCT SPEC 108-71032

APPLICATION SPEC SEE TABLE

WEIGHT -

 Tyco Electronics
CH - Switzerland - Lugano

NAME

CABLE PLUG
SNAP-ON COUPLING
1.0/2.3 75 Ohm

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C5-1393670-7

-

SCALE 5:1

SHEET 3 OF 3

REV B6

AMP 1470-19 REV 31MAR2000