


O.P. (MM)	P.T. (MM)
10.8±0.8	2.0 MAX.




O.P. = OPERATING POINT
P.T. = PRE-TRAVEL

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- ▲ 3. RATING: RATING: 0.4VA MAX. @ 20VDC MAX.
- ▲ 4. OPERATING FORCE: 25 ± 10 gf
5. OPERATING TEMP: -25°C to 75°C
6. ELECTRICAL LIFE: 10,000 CYCLES MIN.
7. MECHANICAL LIFE: 500,000 CYCLES MIN.
8. CONTACT RESISTANCE: 100 milleOHMS MAX.
9. INSULATION RESISTANCE: 100 MEGA-OHMS MIN.
10. DIELECTRIC STRENGTH: 500VAC - 1 MINUTE
11. ▲ DENOTES CRITICAL PARAMETER.
12. PACKAGED IN TRAYS, 120 PIECES PER TRAY.



E-SWITCH LOGO
LOCATION



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
A	ECO-100567	Release	11/29/21	MW	TITLE SS075R102F025S1A				100120075
					SCALE	DATE	DR	DWG	REV
					4:1	11/22/2021	MW	Q971045	A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED